


Captive Screw Type 2 1/4-20 Thread



Create a part number:

Length	Material	Finish
FCXXXX	XX	XX
_____ - _____ - _____		

Captive Screws - 1/4-20 Thread				
✓	FCXXXX	Length (L)	S.L. +.010 -.010	D. +.010 -.000
	FC0467	5/8	1/8	.093
	FC0468	11/16	3/16	.093
	FC0469	3/4	1/4	.093
	FC0470	13/16	5/16	.093
	FC0471	7/8	3/8	.093
	FC0472	15/16	7/16	.093
	FC0473	1	1/2	.093
	FC0474	1-1/16	9/16	.093
	FC0475	1-1/8	5/8	.093
	FC0476	1-3/16	11/16	.093
	FC0477	1-1/4	3/4	.093
	FC0478	1-5/16	13/16	.093
	FC0479	1-3/8	7/8	.093
	FC0480	1-7/16	15/16	.093
	FC0481	1-1/2	1	.093
	FC0482	1-9/16	1-1/6	.093
	FC0483	1-5/8	1-1/8	.093
	FC0484	1-11/16	1-3/16	.093
	FC0485	1-3/4	1-1/4	.093
	FC0486	1-13/16	1-5/16	.093
	FC0487	1-7/8	1-3/8	.093
	FC0488	1-15/16	1-7/16	.093
	FC0489	2	1-1/2	.093

Material		
✓	Material Code (XX)	
	B	Brass
	S	Steel
	SS	Stainless Steel

✓	Compatible Finish (XX)	
	B, S, SS	0 - Plain
	B, S	5 - Nickel Plate (QQ-N-290)
	B, S	12 - Zinc Clear (ASTM-B-633)
	B, S	16 - Electro Tin (MIL-T-10727 TYPE 1)
	SS	20 - Passivation (MIL-F-14072D)
	B, S, SS	26 - Black Oxide
	B, S	28 - Zinc Yellow (ASTM-B-633)

Source Control Drawing:
To be produced by
Fascomp Electronic Hardware

Tolerances
Unless otherwise Specified
.xxx +/- .005
.xx +/- .010
Angular +/- 1 Degree
Linear +/- .005
Break all sharp edges



This document is the property of Fascomp Inc. and shall not be reproduced, distributed, or used as a basis for manufacturing without written permission from Fascomp Inc.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Fascomp:

[FC0467-SS](#) [FC0468-SS](#) [FC0469-SS](#) [FC0470-SS](#) [FC0471-SS](#) [FC0472-SS](#) [FC0473-SS](#)