



Main

| | |
|------------------------------------|-------------------|
| Accessory / separate part category | Cabling accessory |
| Accessory / Separate Part Type | Jumper cable |

Complementary

| | |
|-------------------------------------|-------------------------------------|
| Jumper cable end 1 | M12 male 4 pins straight screw-on |
| Jumper cable end 2 | M12 female 4 pins straight screw-on |
| Collar material | Metal |
| Cable composition | 4 x 0.34 mm ² |
| Cable length | 16.40 ft (5 m) |
| Wire insulation material | PUR shielded cable) |
| Cable outer diameter | 0.23 in (5.9 mm) |
| [Ue] rated operational voltage | 250 V AC 300 V DC |
| Line Rated Current | 4 A |
| Insulation resistance | >= 1000 MOhm |
| Maximum resistance across terminals | 5000 mOhm |
| Net Weight | 1.10 lb(US) (0.5 kg) |

Environment

| | |
|---------------------------------------|-----------------------------------|
| IP Degree of Protection | IP67 IP65 |
| Ambient air temperature for operation | -13...176 °F (-25...80 °C) static |
| Ambient Air Temperature for Storage | -13...176 °F (-25...80 °C) |

Ordering and shipping details

| | |
|-------------------|----------------------|
| Category | 22483-MACHINE CABLES |
| Discount Schedule | DS3 |
| GTIN | 3389119621793 |
| Returnability | No |

Packing Units


| | |
|------------------------------|-------------------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 1.18 in (3.0 cm) |
| Package 1 Width | 6.89 in (17.5 cm) |
| Package 1 Length | 7.09 in (18.0 cm) |
| Package 1 Weight | 8.92 oz (253.0 g) |
| Unit Type of Package 2 | S02 |

| | |
|------------------------------|-------------------------|
| Number of Units in Package 2 | 20 |
| Package 2 Height | 5.91 in (15.0 cm) |
| Package 2 Width | 11.81 in (30.0 cm) |
| Package 2 Length | 15.75 in (40.0 cm) |
| Package 2 Weight | 11.79 lb(US) (5.348 kg) |


Offer Sustainability

| | |
|----------------------------|---|
| California proposition 65 | WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information | Yes |

Dimensions



Connections and Schemes



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Telemecanique Sensors:](#)

[XZCRB151141C5](#)