





Main

Range of Product	Telemecanique Limit switches XC Standard
Series name	Standard format
Product or Component Type	Limit switch head
Device short name	ZCE
Head type	Rotary head
Product Compatibility	XCKD XCKP XCKT XCMD
Associated lever	ZCY45 ZCY53 ZCY44 ZCY69 ZCY46 ZCY18 ZCY49 ZCY26 ZCY81 ZCY22 ZCY23 ZCY91 ZCY48 ZCY39 ZCY17 ZCY12 ZCY16 ZCY25 ZCY15 ZCY59 ZCY54 ZCY55 ZCY19

Associated body	ZCMD41L5 ZCMD39L2 ZCT26P16 ZCMD69C12 ZCT28N12 ZCD21 ZCMD61C12 ZCP25 ZCT28P16 ZCD37 ZCT25G11 ZCP21 ZCMD25L5 ZCMD39L5 ZCT28G11 ZCT26G11 ZCMD37L5 ZCMD81L5 ZCT27P16 ZCP29M12 ZCP31 ZCP21M12 ZCP37 ZCMD25L2 ZCMD21M12 ZCT27N12 ZCMD21L08R12 ZCD26 ZCT25P16 ZCMD21L08U78 ZCMD41L1 ZCMD37L1 ZCP27 ZCMD37L2 ZCMD41L2 ZCP28 ZCT21P16 ZCD39 ZCMD21C12 ZCMD21L1 ZCD28 ZCT21G11 ZCMD61M12 ZCP35 ZCD31 ZCMD25L1 ZCP26 ZCT26N12 ZCMD39L1 ZCP29 ZCD25 ZCT21N12 ZCD29M12 ZCD21M12 ZCMD81L2 ZCMD21L5 ZCP39 ZCMD81L1 ZCMD29L1 ZCT27G11 ZCD29 ZCMD29L5 ZCD27 ZCMD21L2 ZCMD29C12 ZCMD29L2 ZCT25N12 ZCD35
Movement of operating head	Rotary
Type of operator	Without operating lever spring return metal
Type of approach	Lateral approach, 2 directions

Complementary

Positive opening	With
------------------	------

Environment

Ambient Air Temperature for Operation	-13...158 °F (-25...70 °C)
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Environmental characteristic	Standard environment

Ordering and shipping details

Category	22413-LIMIT SWITCH, IEC, MINIATURE
Discount Schedule	T
GTIN	3389110191547
Returnability	Yes
Country of origin	ID

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.60 in (1.524 cm)
Package 1 Width	2.75 in (6.985 cm)
Package 1 Length	6.50 in (16.51 cm)
Package 1 Weight	1.41 oz (39.92 g)
Unit Type of Package 2	BAG
Number of Units in Package 2	10
Package 2 Height	5.91 in (15 cm)
Package 2 Width	1.97 in (5 cm)
Package 2 Length	3.94 in (10 cm)
Package 2 Weight	14.48 oz (410.5 g)
Unit Type of Package 3	P06
Number of Units in Package 3	3840
Package 3 Height	31.50 in (80 cm)
Package 3 Width	31.50 in (80 cm)
Package 3 Length	23.62 in (60 cm)
Package 3 Weight	373.24 lb(US) (169.3 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Telemecanique Sensors:](#)

[ZCE01](#)