





Main

Range of Product	Telemecanique Limit switches XC Standard
Series name	Standard format
Product or Component Type	Limit switch head
Device short name	ZCE
Head type	Multi-directional head
Product Compatibility	XCKP XCKD XCMD XCKT

Associated body	ZCT21P16 ZCMD37L1 ZCMD81L1 ZCP28 ZCMD21C12 ZCT27G11 ZCT25N12 ZCT27P16 ZCD31 ZCMD39L5 ZCMD37L2 ZCD26 ZCP35 ZCMD29L5 ZCMD29L1 ZCT21N12 ZCMD61M12 ZCMD39L1 ZCD35 ZCMD21L2 ZCT26G11 ZCT27N12 ZCP27 ZCP21M12 ZCMD29L2 ZCT26N12 ZCD29 ZCD21M12 ZCMD21L5 ZCT28P16 ZCT26P16 ZCP37 ZCP25 ZCMD29C12 ZCMD25L2 ZCT28G11 ZCMD21L1 ZCP31 ZCMD41L2 ZCD29M12 ZCMD39L2 ZCT25G11 ZCD25 ZCMD81L2 ZCMD37L5 ZCD21 ZCMD25L5 ZCMD61C12 ZCMD69C12 ZCT28N12 ZCMD21L08U78 ZCD27 ZCMD81L5 ZCMD41L5 ZCD28 ZCMD25L1 ZCP21 ZCT21G11 ZCP29M12 ZCMD21L08R12 ZCMD41L1 ZCMD21M12 ZCT25P16 ZCP26 ZCP29 ZCD39 ZCP39 ZCD37
Movement of operating head	Multi-directional
Type of operator	Spring rod spring return metal with nitrile boot)
Type of approach	Multi-directional approach

Complementary

Switch actuation	By any moving part
Positive opening	Without

Environment

Ambient Air Temperature for Operation	-13...158 °F (-25...70 °C)
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Environmental characteristic	Standard environment

Ordering and shipping details

Category	22413-LIMIT SWITCH, IEC, MINIATURE
Discount Schedule	T
GTIN	3389110191066
Nbr. of units in pkg.	1
Package weight(Lbs)	0.85 oz (24.0 g)
Returnability	Yes
Country of origin	ID

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	0.79 in (2 cm)
Package 1 width	5.00 in (12.7 cm)
Package 1 Length	0.67 in (1.7 cm)
Unit Type of Package 2	S01
Number of Units in Package 2	80
Package 2 Weight	4.23 lb(US) (1.92 kg)
Package 2 Height	5.91 in (15 cm)
Package 2 width	5.91 in (15 cm)
Package 2 Length	15.75 in (40 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Telemecanique Sensors:](#)

[ZCE08](#)