



Main

Range of Product	Telemecanique Limit switches XC Standard
Series name	Standard format
Product or Component Type	Limit switch head
Device short name	ZCKE
Head type	Rotary head
Product Compatibility	XCKJ
Associated lever	ZCKY91 ZCKY52 ZCKY53 ZCKY11 ZCKY13 ZCKY43 ZCKY51 ZCKY14 ZCKY81 ZCKY41 ZCKY59
Associated body	ZCKJD37H7 ZCKJ5H29 ZCKJ8H7 ZCKJ1H29 ZCKJ8 ZCKJ7 ZCKJ41 ZCKJ6H29 ZCKJ11H29 ZCKJ41H29 ZCKJ11H7 ZCKJD35H7 ZCKJD31H7 ZCKJ9H29 ZCKJD31H29 ZCKJ21 ZCKJD39H7 ZCKJ9H7 ZCKJ4H29 ZCKJD35H29 ZCKJ6 ZCKJ11 ZCKJ5 ZCKJ7H29 ZCKJ1H7 ZCKJ7H7 ZCKJ9 ZCKJ8H29 ZCKJ6H7 ZCKJ4104H29 ZCKJD31 ZCKJ4104H7 ZCKJ5H7 ZCKJ2H7 ZCKJ404H29 ZCKJD37H29 ZCKJ4 ZCKJ21H7 ZCKJ1 ZCKJ2H29 ZCKJD39H29 ZCKJD37 ZCKJ2 ZCKJD35 ZCKJ41H7 ZCKJ404 ZCKJD39 ZCKJ4104 ZCKJ21H29 ZCKJ4H7 ZCKJ404H7
Movement of operating head	Rotary

Type of operator	Without operating lever spring return
Type of approach	Lateral approach, 1 or 2 programmable direction

Complementary

Switch actuation	From left and/or right CW and/or CCW
Positive opening	With
Head material	Metal

Environment

Ambient Air Temperature for Operation	-13...158 °F (-25...70 °C)
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Environmental characteristic	Standard environment

Ordering and shipping details

Category	22411-LIMIT SWITCHES,IEC,XCKJ
Discount Schedule	T
GTIN	3389110646252
Returnability	Yes
Country of origin	ID

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.65 in (4.200 cm)
Package 1 Width	1.81 in (4.600 cm)
Package 1 Length	3.43 in (8.700 cm)
Package 1 Weight	5.93 oz (168.000 g)
Unit Type of Package 2	S01
Number of Units in Package 2	27
Package 2 Height	5.91 in (15.000 cm)
Package 2 Width	5.91 in (15.000 cm)
Package 2 Length	15.75 in (40.000 cm)
Package 2 Weight	10.57 lb(US) (4.794 kg)
Unit Type of Package 3	P06
Number of Units in Package 3	864
Package 3 Height	30.31 in (77.000 cm)
Package 3 Width	31.50 in (80.000 cm)
Package 3 Length	23.62 in (60.000 cm)
Package 3 Weight	354.62 lb(US) (160.852 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Telemecanique Sensors:](#)

[ZCKE05](#)