

ZCKE09

Limit switch head, Limit switches XC Standard, ZCKE, w/o lever stay put left and right actuation



Main

Range of Product	Telemecanique Limit switches XC Standard
Series name	Standard format
Product or Component Type	Limit switch head
Device short name	ZCKE
Head type	Rotary head
Product Compatibility	XCKJ
Associated lever	ZCKY71 ZCKY61
Associated body	ZCKJD39 ZCKJ2H7 ZCKJ21H29 ZCKJ9H29 ZCKJ1 ZCKJ21 ZCKJ1H29 ZCKJ2 ZCKJD31H7 ZCKJ11H29 ZCKJ11H7 ZCKJ9H7 ZCKJ2H29 ZCKJD39H7 ZCKJ9 ZCKJ1H7 ZCKJD39H29 ZCKJD31H29 ZCKJ11 ZCKJ21H7 ZCKJD31
Movement of operating head	Rotary
Type of operator	Stay put without operating lever stay put
Type of approach	Lateral approach, 2 directions

Complementary

Switch actuation	From left and right
Positive opening	With
Head material	Metal

Environment

Ambient Air Temperature for Operation	-13...158 °F (-25...70 °C)
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Environmental characteristic	Standard environment

Ordering and shipping details

Category	22411-LIMIT SWITCHES,IEC,XCKJ
Discount Schedule	T
GTIN	3389110646276
Returnability	Yes
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.57 in (4 cm)
Package 1 Width	2.28 in (5.8 cm)
Package 1 Length	4.49 in (11.4 cm)
Package 1 Weight	6.88 oz (195 g)
Unit Type of Package 2	S01
Number of Units in Package 2	24
Package 2 Height	5.91 in (15 cm)
Package 2 Width	5.91 in (15 cm)
Package 2 Length	15.75 in (40 cm)
Package 2 Weight	10.91 lb(US) (4.947 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Diisodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Telemecanique Sensors:](#)

[ZCKE09](#)