



JUMPERS



Terminal Block Series	Cat. No.	Std. Pk.	Blue	Red
CP1.5 Series	JX1.5/2	100	JX1.5/2/BU	JX1.5/2/R
CPG1.5 Series	JX1.5/3	50	JX1.5/3/BU	JX1.5/3/R
CPDL1.5 Series	JX1.5/4	50	JX1.5/4/BU	JX1.5/5/R
CPST1.5 Series	JX1.5/10	10	JX1.5/10/BU	JX1.5/10/R
	JX2.5/2	100	—	—
	JX2.5/3	50	—	—
CP2.5 Series	JX2.5/4	50	—	—
CPG2.5 Series	JX2.5/5	50	—	—
CPDL2.5 Series	JX2.5/6	50	—	—
CPDLK2.5 Series	JX2.5/7	50	—	—
	JX2.5/8	50	—	—
	JX2.5/10	10	—	—
	JX4/2	100	—	—
	JX4/3	50	—	—
CP4 Series	JX4/4	50	—	—
CPG4 Series	JX4/8	50	—	—
	JX4/10	50	—	—
	JX4/16	50	—	—
	JX6/2	100	—	—
CP6/10 Series	JX6/3	50	—	—
CPG6/10 Series	JX6/4	50	—	—
	JX6/10	10	—	—
	CA801/A2	100	—	—
CP3L2.5 Series	CA801/A3	100	—	—
CP4LG2.5 Series	CA801/A5	100	—	—
	CA801/A10	10	—	—



- A Standardized in various pole configurations
- B Easy breakout pins to skip terminals
- C 2 jumper channels for various circuit options
- D Step down jumpers to short different wire size terminals
- E Felt-tip pen marking area



STEP DOWN JUMPERS

Used for jumpering terminal blocks of different sizes.


Jumper for	Cat. No.	Std. Pk.
CP6 to CP2.5	JXS6/2.5	50
CP4 to CP2.5	JXS4/2.5	50
CP6 to CP4	JXS6/4	50

ENDPLATES




Terminal Block	Cat. No.	Dimensions	Std. Pk.
CP1.5	EPCP1.5	26.35 x 45.3 x 1.5 mm	50
CPG1.5	EPCP1.5	26.35 x 45.3 x 1.5 mm	50
CP2.5	EPCX2.5	30.5 x 49.7 x 1.5 mm	50
CPG2.5	EPCX2.5	30.5 x 49.7 x 1.5 mm	50
CP4	EPCX4	30.5 x 54.8 x 1.5 mm	50
CPG4	EPCX4	30.5 x 54.8 x 1.5 mm	50
CP6/10	EPCX6	35.3 x 62.1 x 1.5 mm	50
CPG6/10	EPCX6	35.3 x 62.1 x 1.5 mm	50
CP1.5/3	EPCP1.5/3	26.35 x 54.4 x 1.5 mm	50
CPG1.5/3	EPCP1.5/3	26.35 x 54.4 x 1.5 mm	50
CP2.5/3	EPCX2.5/3	30.5 x 62.2 x 1.5 mm	50
CPG2.5/3	EPCX2.5/3	30.5 x 62.2 x 1.5 mm	50
CP4/3	EPCX4/3	30.5 x 70.5 x 1.5 mm	50
CPG4/3	EPCX4/3	30.5 x 70.5 x 1.5 mm	50
CP6/10/3	EPCX6/3	35.3 x 82.2 x 1.5 mm	50
CPG6/10/3	EPCX6/3	35.3 x 82.2 x 1.5 mm	50
CPDL1.5	EPCPDL1.5	37.5 x 67.2 x 1.5 mm	50
CPDLG1.5	EPCPDL1.5	37.5 x 67.2 x 1.5 mm	50
EPCX2.5	EPCXDL2.5	41.8 x 72.7 x 1.5mm	50
EPCXG2.5	EPCXDL2.5	41.8 x 72.7 x 1.5mm	50
CP3L2.5	EPCP3L2.5	98.70 x 83 x 1.5 mm	50
CP3LG2.5	EPCP3L2.5	98.70 x 83 x 1.5 mm	50
CPDLK2.5	EPCPDLK2.5	107 x 38.1 x 1.5 mm	50
CPST1.5/3	EPCPPT2.5/3	96.5 x 40.3 x 1.5 mm	50
CPPT2.5/3	EPCPPT2.5/3	96.5 x 40.3 x 1.5 mm	50
CPST1.5/4	EPCPPT2.5/4	58.1 x 69.5 x 1.5 mm	50
CPPTG2.5/4	EPCPPT2.5/4	58.1 x 69.5 x 1.5 mm	50

PARTITION PLATES




Terminal Block	Cat. No.	Dimensions	Std. Pk.
CP1.5, CP2.5, CP4, CPG1.5, CPG2.5, CPG4	PPCX4	42.4 x 59 x 2mm	50
CP6/10	PPCX10	53.5 x 76 x 1mm	50
CPG6/10	PPCX10	53.5 x 76 x 1mm	50
CP1.5/3, CP2.5/3, CP4/3, CPG1.5/3, CPG2.5/3, CPG4/3	PPCX4/3	42.4 x 47.7 x 2mm	50
CP1.5/4, CP2.5/4, CP4/4, CPG1.5/4, CPG2.5/4, CPG4/4	PPCX4/4	42.4 x 95 x 2mm	50

END STOPS



Screwless
Snap On



Cat. No.	Dimensions	Std. Pk.	Cat. No.	Dimensions	Std. Pk.
CA103	35 x 41 x 6mm	50	CA702	34 x 45 x 9mm	50
CA104	41 x 36 x 10mm	50			



Cat. No.	Dimensions	Std. Pk.
CA802	32 x 45 x 8mm	50

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Altech:](#)

[JX1.5/10](#) [JX1.5/10/BU](#) [JX1.5/10/R](#) [JX1.5/2](#) [JX1.5/2/BU](#) [JX1.5/2/R](#) [JX1.5/3](#) [JX1.5/3/BU](#) [JX1.5/3/R](#) [JX1.5/4](#)
[JX1.5/4/BU](#) [JX1.5/4/R](#) [EPCPDL1.5](#)