



### JUMPERS



| Terminal Block Series | Cat. No.  | Std. Pk. | Blue        | Red        |
|-----------------------|-----------|----------|-------------|------------|
| CP1.5 Series          | JX1.5/2   | 100      | JX1.5/2/BU  | JX1.5/2/R  |
| CPG1.5 Series         | JX1.5/3   | 50       | JX1.5/3/BU  | JX1.5/3/R  |
| CPDL1.5 Series        | JX1.5/4   | 50       | JX1.5/4/BU  | JX1.5/5/R  |
| CPST1.5 Series        | JX1.5/10  | 10       | JX1.5/10/BU | JX1.5/10/R |
|                       | JX2.5/2   | 100      | —           | —          |
|                       | JX2.5/3   | 50       | —           | —          |
| CP2.5 Series          | JX2.5/4   | 50       | —           | —          |
| CPG2.5 Series         | JX2.5/5   | 50       | —           | —          |
| CPDL2.5 Series        | JX2.5/6   | 50       | —           | —          |
| CPDLK2.5 Series       | JX2.5/7   | 50       | —           | —          |
|                       | JX2.5/8   | 50       | —           | —          |
|                       | JX2.5/10  | 10       | —           | —          |
|                       | JX4/2     | 100      | —           | —          |
|                       | JX4/3     | 50       | —           | —          |
| CP4 Series            | JX4/4     | 50       | —           | —          |
| CPG4 Series           | JX4/8     | 50       | —           | —          |
|                       | JX4/10    | 50       | —           | —          |
|                       | JX4/16    | 50       | —           | —          |
|                       | JX6/2     | 100      | —           | —          |
| CP6/10 Series         | JX6/3     | 50       | —           | —          |
| CPG6/10 Series        | JX6/4     | 50       | —           | —          |
|                       | JX6/10    | 10       | —           | —          |
|                       | CA801/A2  | 100      | —           | —          |
| CP3L2.5 Series        | CA801/A3  | 100      | —           | —          |
| CP4LG2.5 Series       | CA801/A5  | 100      | —           | —          |
|                       | CA801/A10 | 10       | —           | —          |



- A Standardized in various pole configurations
- B Easy breakout pins to skip terminals
- C 2 jumper channels for various circuit options
- D Step down jumpers to short different wire size terminals
- E Felt-tip pen marking area



### STEP DOWN JUMPERS

Used for jumpering terminal blocks of different sizes.


| Jumper for   | Cat. No. | Std. Pk. |
|--------------|----------|----------|
| CP6 to CP2.5 | JXS6/2.5 | 50       |
| CP4 to CP2.5 | JXS4/2.5 | 50       |
| CP6 to CP4   | JXS6/4   | 50       |

### ENDPLATES




| Terminal Block | Cat. No.    | Dimensions            | Std. Pk. |
|----------------|-------------|-----------------------|----------|
| CP1.5          | EPCP1.5     | 26.35 x 45.3 x 1.5 mm | 50       |
| CPG1.5         | EPCP1.5     | 26.35 x 45.3 x 1.5 mm | 50       |
| CP2.5          | EPCX2.5     | 30.5 x 49.7 x 1.5 mm  | 50       |
| CPG2.5         | EPCX2.5     | 30.5 x 49.7 x 1.5 mm  | 50       |
| CP4            | EPCX4       | 30.5 x 54.8 x 1.5 mm  | 50       |
| CPG4           | EPCX4       | 30.5 x 54.8 x 1.5 mm  | 50       |
| CP6/10         | EPCX6       | 35.3 x 62.1 x 1.5 mm  | 50       |
| CPG6/10        | EPCX6       | 35.3 x 62.1 x 1.5 mm  | 50       |
| CP1.5/3        | EPCP1.5/3   | 26.35 x 54.4 x 1.5 mm | 50       |
| CPG1.5/3       | EPCP1.5/3   | 26.35 x 54.4 x 1.5 mm | 50       |
| CP2.5/3        | EPCX2.5/3   | 30.5 x 62.2 x 1.5 mm  | 50       |
| CPG2.5/3       | EPCX2.5/3   | 30.5 x 62.2 x 1.5 mm  | 50       |
| CP4/3          | EPCX4/3     | 30.5 x 70.5 x 1.5 mm  | 50       |
| CPG4/3         | EPCX4/3     | 30.5 x 70.5 x 1.5 mm  | 50       |
| CP6/10/3       | EPCX6/3     | 35.3 x 82.2 x 1.5 mm  | 50       |
| CPG6/10/3      | EPCX6/3     | 35.3 x 82.2 x 1.5 mm  | 50       |
| CPDL1.5        | EPCPDL1.5   | 37.5 x 67.2 x 1.5 mm  | 50       |
| CPDLG1.5       | EPCPDL1.5   | 37.5 x 67.2 x 1.5 mm  | 50       |
| EPCX2.5        | EPCXDL2.5   | 41.8 x 72.7 x 1.5mm   | 50       |
| EPCXG2.5       | EPCXDL2.5   | 41.8 x 72.7 x 1.5mm   | 50       |
| CP3L2.5        | EPCP3L2.5   | 98.70 x 83 x 1.5 mm   | 50       |
| CP3LG2.5       | EPCP3L2.5   | 98.70 x 83 x 1.5 mm   | 50       |
| CPDLK2.5       | EPCPDLK2.5  | 107 x 38.1 x 1.5 mm   | 50       |
| CPST1.5/3      | EPCPPT2.5/3 | 96.5 x 40.3 x 1.5 mm  | 50       |
| CPPT2.5/3      | EPCPPT2.5/3 | 96.5 x 40.3 x 1.5 mm  | 50       |
| CPST1.5/4      | EPCPPT2.5/4 | 58.1 x 69.5 x 1.5 mm  | 50       |
| CPPTG2.5/4     | EPCPPT2.5/4 | 58.1 x 69.5 x 1.5 mm  | 50       |

### PARTITION PLATES




| Terminal Block                                      | Cat. No. | Dimensions        | Std. Pk. |
|-----------------------------------------------------|----------|-------------------|----------|
| CP1.5, CP2.5, CP4, CPG1.5, CPG2.5, CPG4             | PPCX4    | 42.4 x 59 x 2mm   | 50       |
| CP6/10                                              | PPCX10   | 53.5 x 76 x 1mm   | 50       |
| CPG6/10                                             | PPCX10   | 53.5 x 76 x 1mm   | 50       |
| CP1.5/3, CP2.5/3, CP4/3, CPG1.5/3, CPG2.5/3, CPG4/3 | PPCX4/3  | 42.4 x 47.7 x 2mm | 50       |
| CP1.5/4, CP2.5/4, CP4/4, CPG1.5/4, CPG2.5/4, CPG4/4 | PPCX4/4  | 42.4 x 95 x 2mm   | 50       |

### END STOPS



Screwless  
Snap On



| Cat. No. | Dimensions     | Std. Pk. | Cat. No. | Dimensions    | Std. Pk. |
|----------|----------------|----------|----------|---------------|----------|
| CA103    | 35 x 41 x 6mm  | 50       | CA702    | 34 x 45 x 9mm | 50       |
| CA104    | 41 x 36 x 10mm | 50       |          |               |          |



| Cat. No. | Dimensions    | Std. Pk. |
|----------|---------------|----------|
| CA802    | 32 x 45 x 8mm | 50       |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Altech:](#)

[EPCPDLK2.5](#) [EPCPPT2.5/3](#) [EPCPPT2.5/4](#)