


SN2 Series

HW




Switching Operation

1 NC / 1 NO Contacts


Slow Action

603.3121.007
SN2-U1Z HW



Snap Action

603.3371.006
SN2-SU1Z HW



2 NC Contacts

-

-

2 NO Contacts

-

-

1 NC / 1 NO Contacts Overlapping

-

-

Replacement actuator:

391.3210.553

Technical Information

Slow Action

Snap Action

Maximum Switching Voltage	240V
Max. Switching Amps (up to)*	10A
B10d (up to)*	20 Million
Mechanical Service Life (up to)*	3 x 10 ⁶
Switching Frequency	≤ 100/min
Operating Temperature	-30 °C to +80 °C
Protection Rating	IP65
Utilization Category (up to)*	AC-15, Ue/Ue 240V 3A
Rate Insulation Voltage	400VAC


Maximum Switching Voltage	240V
Max. Switching Amps (up to)*	10A
B10d (up to)*	20 Million
Mechanical Service Life (up to)*	10 x 10 ⁶
Switching Frequency	≤ 100/min
Operating Temperature	-30 °C to +80 °C
Protection Rating	IP65
Utilization Category (up to)*	AC-15, Ue/Ue 240V 3A
Rate Insulation Voltage	400VAC

Approvals

* Depending on switching system - see technical information for details



AD4K




Slow Action

Snap Action

613.3887.022
SN2-SA2Z AD4K

Functional description of turnstile



Slow Action

Snap Action

Maximum Switching Voltage	240V
Max. Switching Amps (up to)*	10A
B10d (up to)*	20 Million
Mechanical Service Life (up to)*	10 x 10 ⁶
Switching Frequency	≤ 100/min
Operating Temperature	-30 °C to +80 °C
Protection Rating	IP65
Utilization Category (up to)*	AC-15, Ue/Ue 240V 3A
Rate Insulation Voltage	400VAC

Maximum Switching Voltage	240V
Max. Switching Amps (up to)*	10A
B10d (up to)*	20 Million
Mechanical Service Life (up to)*	10 x 10 ⁶
Switching Frequency	≤ 100/min
Operating Temperature	-30 °C to +80 °C
Protection Rating	IP65
Utilization Category (up to)*	AC-15, Ue/Ue 240V 3A
Rate Insulation Voltage	400VAC



Special features/variants (on request)

- Available with different actuating directions

Drawing dimensions in mm

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Altech:](#)

[613.3887.022](#) [603.3371.006](#) [603.3121.007](#)