

Adapter, Metric to PG Thread, Nickel-Plated Brass

Material:

- Nickel-plated brass
- O-ring: Nitril

Characteristics:

- Metric external thread
- PG internal thread
- Hexagon

External thread	Internal thread	SW mm	Thread length mm	Complete length mm	Cat. No. without O-ring	Cat. No. with O-ring	Std. Pk.
Form A							
Metric	PG						
M 12 x 1.5	PG 7	14	7	17	6604712	6604658	100
M 16 x 1.5	PG 9	18	7	17.5	6604716	6604660	50
M 16 x 1.5	PG 11	20	7	18	6604715	6604661	50
M 16 x 1.5	PG 13.5	22	7	19.5	6604709	6604662	50
M 16 x 1.5	PG 16	24	7	21.5	6604717	6604663	50
M 20 x 1.5	PG 11	22	7	18	6604720	6604666	50
M 20 x 1.5	PG 13.5	22	7	19.5	6604721	6604664	50
M 20 x 1.5	PG 16	24	7	20.5	6604722	6604667	50
M 20 x 1.5	PG 21	32	7	22.5	6604708	6604668	50
M 25 x 1.5	PG 16	27	8	21.5	6604726	6604669	50
M 25 x 1.5	PG 21	32	8	23.0	6604725	6604670	50
M 25 x 1.5	PG 29	40	8	25	6604727	6604676	20
M 32 x 1.5	PG 21	34	8.5	23.5	6604729	6604672	20
M 32 x 1.5	PG 29	40	8.5	25.0	6604732	6604681	10
M 40 x 1.5	PG 29	42	8.5	25	6604734	6604675	10
M 40 x 1.5	PG 36	50	8.5	28.0	6604740	6604685	10
M 50 x 1.5	PG 36	52	9.5	29	6604742	6604678	10
M 50 x 1.5	PG 42	58	9.5	31.5	6604750	6604689	5
M 63 x 1.5	PG 42	65	10.5	32.5	6604752	6604692	1
M 63 x 1.5	PG 48	65	10.5	32.5	6604763	6604694	1
M 75 x 1.5	PG 48	80	11.5	34.5	6604764	6604695	1
Form B							
M 16 x 1.5	PG 7	18	7	10.5	6604713	6604659	100
M 20 x 1.5	PG 9	22	7	11	6604719	6604665	50
M 25 x 1.5	PG 9	27	8	12	6604707	6604674	50
M 25 x 1.5	PG 11	27	8	12	6604723	6604671	50
M 25 x 1.5	PG 13.5	27	8	12	6604724	6604673	50
M 32 x 1.5	PG 13.5	34	8.5	12.5	6604706	6604677	20
M 32 x 1.5	PG 16	34	8.5	12.5	6604728	6604679	20
M 32 x 1.5	PG 21	34	8.5	12.5	6604730	6604680	20
M 40 x 1.5	PG 16	42	8.5	13.5	6604705	6604682	10
M 40 x 1.5	PG 21	42	8.5	13.5	6604733	6604683	10
M 40 x 1.5	PG 29	42	8.5	13.5	6604735	6604684	20
M 50 x 1.5	PG 21	52	9.5	15.5	6604704	6604686	10
M 50 x 1.5	PG 29	52	9.5	15.5	6604741	6604687	10
M 50 x 1.5	PG 36	52	9.5	15.5	6604743	6604688	10
M 63 x 1.5	PG 29	65	10.5	17.5	6604703	6604690	5
M 63 x 1.5	PG 36	65	10.5	17.5	6604751	6604691	5
M 63 x 1.5	PG 42	65	10.5	17.5	6604753	6604693	5



Form A



Form B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Altech:

[6604722](#) [6604728](#) [6604724](#) [6604730](#) [6604706](#) [6604721](#) [6604726](#) [6604742](#) [6604729](#) [6604733](#) [6604725](#)
[6604750](#) [6604732](#) [6604712](#) [6604735](#) [6604709](#) [6604715](#) [6604716](#) [6604708](#) [6604704](#) [6604720](#) [6604727](#)
[6604719](#) [6604705](#) [6604763](#)