


1 PHASE BUSBAR - 1/2 pole spacing

18mm² for 80A


Altech Corp.®



18mm ² for 80A			
Type/ Cat. No.	No. of Pins	No. of MMC to Jumper	Length [mm]
1P18U1H/2	2	2x1 pole	39.0
1P18U1H/3	3	3x1 pole	66.0
1P18U1H/4	4	4x1 pole	93.0
1P18U1H/5	5	5x1 pole	120.0
1P18U1H/6	6	6x1 pole	147.0
1P18U1H/7	7	7x1 pole	174.0
1P18U1H/8	8	8x1 pole	201.0
1P18U1H/9	9	9x1 pole	228.0
1P18U1H/10	10	10x1 pole	255.0
1P18U1H/11	11	11x1 pole	282.0
1P18U1H/12	12	12x1 pole	309.0
1P18U1H/13	13	13x1 pole	336.0
1P18U1H/14	14	14x1 pole	363.0
1P18U1H/15	15	15x1 pole	390.0
1P18U1H/16	16	16x1 pole	417.0
1P18U1H/17	17	17x1 pole	444.0
1P18U1H/18	18	18x1 pole	471.0
1P18U1H/19	19	19x1 pole	498.0

18mm ² for 80A			
Type/ Cat. No.	No. of Pins	No. of MMC to Jumper	Length [mm]
1P18U1H/20	20	20x1 pole	525.0
1P18U1H/21	21	21x1 pole	552.0
1P18U1H/22	22	22x1 pole	579.0
1P18U1H/23	23	23x1 pole	606.0
1P18U1H/24	24	24x1 pole	633.0
1P18U1H/25	25	25x1 pole	660.0
1P18U1H/26	26	26x1 pole	687.0
1P18U1H/27	27	27x1 pole	714.0
1P18U1H/28	28	28x1 pole	741.0
1P18U1H/29	29	29x1 pole	768.0
1P18U1H/30	30	30x1 pole	795.0
1P18U1H/31	31	31x1 pole	822.0
1P18U1H/32	32	32x1 pole	849.0
1P18U1H/33	33	33x1 pole	876.0
1P18U1H/34	34	34x1 pole	903.0
1P18U1H/35	35	35x1 pole	930.0
1P18U1H/36	36	36x1 pole	957.0

ACCESSORIES



Type/Cat. No: **P50UT**
Description: Power Feed Lug



Type/Cat. No: **P50UB**
Description: Modular Direct Power Feed



Type/Cat. No: **BRS5**
Description: Insulation Cap

Altech UL1077

Altech UL508

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Altech:

[1P18U1H/24](#) [1P18U1H/15](#) [1P18U1H/20](#) [1P18U1H/29](#) [1P18U1H/28](#) [1P18U1H/35](#) [1P18U1H/30](#) [1P18U1H/9](#)
[1P18U1H/2](#) [1P18U1H/10](#) [1P18U1H/22](#) [1P18U1H/32](#) [1P18U1H/4](#) [1P18U1H/31](#) [1P18U1H/21](#) [1P18U1H/16](#)
[1P18U1H/37](#) [1P18U1H/7](#) [1P18U1H/8](#) [1P18U1H/12](#) [1P18U1H/11](#) [1P18U1H/13](#) [1P18U1H/3](#) [1P18U1H/6](#)
[1P18U1H/19](#) [1P18U1H/25](#) [1P18U1H/27](#) [1P18U1H/17](#) [1P18U1H/18](#) [1P18U1H/23](#) [1P18U1H/26](#) [1P18U1H/14](#)
[1P18U1H/36](#) [1P18U1H/5](#) [1P18U1H/33](#) [1P18U1H/34](#)