


3 PHASE BUSBAR - standard spacing

18mm² for 80A / 25mm² for 100A



18mm ² for 80A				25mm ² for 100A			
Type/ Cat. No.	No. of Pins	No. of MMC to Jumper	Length [mm]	Type/ Cat. No.	No. of Pins	No. of MMC to Jumper	Length [mm]
3P18U3/6	6	2x3 pole	101.8	3P25U3/6	6	2x3 pole	101.8
3P18U3/9	9	3x3 pole	155.0	3P25U3/9	9	3x3 pole	155.0
3P18U3/12	12	4x3 pole	208.3	3P25U3/12	12	4x3 pole	208.3
3P18U3/15	15	5x3 pole	261.5	3P25U3/15	15	5x3 pole	261.5
3P18U3/18	18	6x3 pole	314.8	3P25U3/18	18	6x3 pole	314.8
3P18U3/21	21	7x3 pole	368.0	3P25U3/21	21	7x3 pole	368.0
3P18U3/24	24	8x3 pole	421.3	3P25U3/24	24	8x3 pole	421.3
3P18U3/27	27	9x3 pole	474.5	3P25U3/27	27	9x3 pole	474.5
3P18U3/30	30	10x3 pole	527.8	3P25U3/30	30	10x3 pole	527.8
3P18U3/33	33	11x3 pole	581.0	3P25U3/33	33	11x3 pole	581.0
3P18U3/36	36	12x3 pole	634.3	3P25U3/36	36	12x3 pole	634.3
3P18U3/39	39	13x3 pole	687.5	3P25U3/39	39	13x3 pole	687.5
3P18U3/42	42	14x3 pole	740.8	3P25U3/42	42	14x3 pole	740.8
3P18U3/45	45	15x3 pole	794.0	3P25U3/45	45	15x3 pole	794.0
3P18U3/48	48	16x3 pole	847.3	3P25U3/48	48	16x3 pole	847.3
3P18U3/51	51	17x3 pole	900.5	3P25U3/51	51	17x3 pole	900.5
3P18U3/54	54	18x3 pole	953.8	3P25U3/54	54	18x3 pole	953.8
3P18U3/57	57	19x3 pole	1007.0	3P25U3/57	57	19x3 pole	1007.0

ACCESSORIES



Type/Cat. No: **P50UT**
Description: Power Feed Lug



Type/Cat. No: **P50UB**
Description: Modular Direct Power Feed



Type/Cat. No: **P95UB**
Description: Power Feed Block



Type/Cat. No: **BRS5**
Description: Insulation Cap



Type/Cat. No: **18/25CAP3P**
Description: End Cap

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Altech:

[18/25CAP3P](#) [3P18U3S/21](#) [3P18U3S/45](#) [3P18U3S/30](#) [3P18U3S/51](#) [3P18U3S/60](#) [3P18U3S/9](#) [3P18U3S/12](#)
[3P18U3S/39](#) [3P18U3S/54](#) [3P25U3S/30](#) [3P18U3S/48](#) [3P18U3S/36](#) [3P18U3S/6](#) [3P25U3S/12](#) [3P25U3S/57](#)
[3P25U3S/9](#) [3P25U3S/21](#) [3P25U3S/42](#) [3P25U3S/33](#) [3P25U3S/48](#) [3P25U3S/18](#) [3P25U3S/60](#) [3P18U3S/24](#)
[3P18U3S/18](#) [3P25U3S/27](#) [3P18U3S/27](#) [3P25U3S/36](#) [3P25U3S/54](#) [3P25U3S/24](#) [3P25U3S/45](#) [3P18U3S/15](#)
[3P25U3S/51](#) [3P25U3S/63](#) [3P18U3S/42](#) [3P18U3S/33](#) [3P25U3S/39](#) [3P25U3S/6](#) [3P18U3S/57](#) [3P18U3S/63](#)
[3P25U3S/15](#)