


22mm LED Illuminated Metal Projecting Operators



Certified for
NEMA Type 4X
12 environment.

Projecting Momentary

with bulb, bulb holder
and mounting bracket



**SAMPLE
ASSEMBLY**



Replacement bulbs
available.
See page 39.

Color 12V AC/DC

Voltage

Cat No.

☐ White	12V AC/DC	2ALP1LB-012
☒ Green	12V AC/DC	2ALP3LB-012
☒ Red	12V AC/DC	2ALP4LB-012
☒ Amber	12V AC/DC	2ALP5LB-012
☒ Blue	12V AC/DC	2ALP6LB-012
☐ Clear	12V AC/DC	2ALP7LB-012
☒ Yellow	12V AC/DC	2ALP8LB-012

24V AC/DC

☐ White	24V AC/DC	2ALP1LB-024
☒ Green	24V AC/DC	2ALP3LB-024
☒ Red	24V AC/DC	2ALP4LB-024
☒ Amber	24V AC/DC	2ALP5LB-024
☒ Blue	24V AC/DC	2ALP6LB-024
☐ Clear	24V AC/DC	2ALP7LB-024
☒ Yellow	24V AC/DC	2ALP8LB-024

48V AC/DC

☐ White	48V AC/DC	2ALP1LB-048
☒ Green	48V AC/DC	2ALP3LB-048
☒ Red	48V AC/DC	2ALP4LB-048
☒ Amber	48V AC/DC	2ALP5LB-048
☒ Blue	48V AC/DC	2ALP6LB-048
☐ Clear	48V AC/DC	2ALP7LB-048
☒ Yellow	48V AC/DC	2ALP8LB-048

110V AC

☐ White	110V AC	2ALP1LB-110
☒ Green	110V AC	2ALP3LB-110
☒ Red	110V AC	2ALP4LB-110
☒ Amber	110V AC	2ALP5LB-110
☒ Blue	110V AC	2ALP6LB-110
☐ Clear	110V AC	2ALP7LB-110
☒ Yellow	110V AC	2ALP8LB-110

110V DC

☐ White	110V DC	2ALP1LB-110D
☒ Green	110V DC	2ALP3LB-110D
☒ Red	110V DC	2ALP4LB-110D
☒ Amber	110V DC	2ALP5LB-110D
☒ Blue	110V DC	2ALP6LB-110D
☐ Clear	110V DC	2ALP7LB-110D
☒ Yellow	110V DC	2ALP8LB-110D

230V AC

☐ White	230V AC	2ALP1LB-230
☒ Green	230V AC	2ALP3LB-230
☒ Red	230V AC	2ALP4LB-230
☒ Amber	230V AC	2ALP5LB-230
☒ Blue	230V AC	2ALP6LB-230
☐ Clear	230V AC	2ALP7LB-230
☒ Yellow	230V AC	2ALP8LB-230

230V DC


☐ White	230V DC	2ALP1LB-230D
☒ Green	230V DC	2ALP3LB-230D
☒ Red	230V DC	2ALP4LB-230D
☒ Amber	230V DC	2ALP5LB-230D
☒ Blue	230V DC	2ALP6LB-230D
☐ Clear	230V DC	2ALP7LB-230D
☒ Yellow	230V DC	2ALP8LB-230D

22mm LED Illuminated Metal Projecting Operators


Dimensional Drawings

All dimensions shown in millimeters.
To convert to inches multiply by 0.03937

Projecting Momentary



Switch Contacts (sold separately)



- Heavy-duty contact blocks with mounting screws. Blocks can be stacked 2 blocks across by 3 blocks deep for a total of 6 circuits.
- Contact blocks are available with silver contacts or gold plated contacts
- Self-wiping contacts

Panel Mount

Normally Open Silver	S1
Normally Closed Silver	S2
Normally Open Gold Plated	S3
Normally Closed Gold Plated	S4


Base Mount*

Normally Open Silver	S5
Normally Closed Silver	S6
Normally Open Gold Plated	S7
Normally Closed Gold Plated	S8

* For use with non-illuminated operators in thermoplastic or aluminum enclosures listed on pages 30 and 36-37.

Exploded Assembly View

- Up to four switch contacts can be installed with any illuminated operator.
- Switch contacts and operators are sold separately. Preassembled push buttons are available on request.



For maintained action use
Cat No. 2PPM.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Altech:](#)

[2ALP7LB-110](#) [2ALP1LB-230](#) [2ALP4LB-012](#) [2ALP1LB-024](#) [2ALP1LB-110](#)