


CDL4U(E)LD4*

AC/ DC voltage indicator with LED

6 mm

54 x 55.5 mm

24V~, 48 V~

9 mm

Polyamide 6.6

 C US	 60947-7-1	 C US E220514
22-10 AWG	0.2-4 sq.mm	22-10 AWG
300 V	500 V	600 V
25 A	32 A	35 A
7 lb-in	0.5 Nm	7 lb-in



Cat. No.	Std. Pk.
----------	----------

CDL4U(E)LD4* 50

EPCDL4U 50




CA702 50
CA802 50

CA727/2 100
CA727/3 100
CA727/4 100
CA727/10 10

CA703/1 100
CA704/1 100
CA705/1 100
CA732/10 100
CA732/10-A 100
CA732/100 10

CA607/S/Q 100

MT2 100


CDL4U(E)LD1/LD2

DC voltage indicator with LED

6 mm

54 x 55.5 mm

24 V-

9 mm

Polyamide 6.6

 C US	 60947-7-1	 C US E220514
22-10 AWG	0.2-4 sq.mm	22-10 AWG
300 V	500 V	600 V
25 A	32 A	35 A
7 lb-in	0.5 Nm	7 lb-in



Cat. No.	Std. Pk.
----------	----------

CDL4U(E)LD1 50
CDL4U(E)LD2 50

EPCDL4U 50





CA702 50
CA802 50

CA727/2 100
CA727/3 100
CA727/4 100
CA727/10 10

CA703/1 100
CA704/1 100
CA705/1 100
CA732/10 100
CA732/10-A 100
CA732/100 10

CA607/S/Q 100

MT2 100


LD1

LD2
CDL4U(E)L1/L2*

DC voltage indicator with LED

6 mm

54 x 55.5 mm

6 V-, 24 V-, 60 V-

9 mm

Polyamide 6.6

 C US	 60947-7-1	 C US E220514
22-10 AWG	0.2-4 sq.mm	22-10 AWG
300 V	500 V	600 V
25 A	32 A	35 A
7 lb-in	0.5 Nm	7 lb-in



Cat. No.	Std. Pk.
----------	----------

CDL4U(E)L1* 50
CDL4U(E)L2* 50

EPCDL4U 50




CA702 50
CA802 50

CA727/2 100
CA727/3 100
CA727/4 100
CA727/10 10

CA703/1 100
CA704/1 100
CA705/1 100
CA732/10 100
CA732/10-A 100
CA732/100 10

CA607/S/Q 100

MT2 100


L1

L2
CDL4U(O)

Electronic Component Carrier

6 mm

54 x 55.5 mm

9 mm

Polyamide 6.6

 C US	 60947-7-1	 C US E220514
22-10 AWG	0.2-4 sq.mm	22-10 AWG
300 V	500 V	600 V
25 A	32 A	35 A
7 lb-in	0.5 Nm	7 lb-in



Cat. No.	Std. Pk.
----------	----------

CDL4U(O) 100

EPCDL4U 50


CA702 50
CA802 50

CA727/2 100
CA727/3 100
CA727/4 100
CA727/10 10

CA703/1 100
CA704/1 100
CA705/1 100
CA732/10 100
CA732/10-A 100
CA732/100 10

CA607/S/Q 100

MT2 100



* Add required voltage to part number as a suffix i.e. CDL4U(E)LD5/110 is for 110V.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Altech:](#)

[CDL4U\(E\)L1](#) [CDL4U\(E\)L2](#) [CDL4U\(O\)](#) [CDL4U\(E\)LD1](#) [CDL4U\(E\)LD2](#) [CDL4U\(E\)LD2/24V](#)