






THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	1/15/16	D.GRIFFIN
B	ECN 8306: UPDATE TO USB TYPE C VERSION 1.2, ADD CONNECTION LINE TO THE WIRE MAP	4/20/16	S.LI



UL STYLE 2725,
(1) 28AWG STRANDED TINNED COPPER TWISTED PAIR
(2) 28AWG STRANDED TINNED COPPER CONDUCTORS
OVERALL ALUMINUM/POLYESTER SHIELD PLUS TINNED
COPPER BRAID SHIELD AND DRAIN WIRE
JACKET: PVC, BLACK (NOM DIA. .126" [3.2])

B

		WIRE MAP				
		"P1"	SIGNAL NAME	CONDUCTOR	"P2"	SIGNAL NAME
	A1,B1,A12,B12	GND	INDV.	5	GND	BLACK
	A4,B4,A9,B9	V _{BUS}	INDV.	1	V _{BUS}	RED
	A5	CC	N/C			
	B5	V _{CONN}	N/C			
	A6	Dp1	UNSHIELDED PAIR	3	D+	GREEN
	A7	Dn1		2	D-	WHITE
	N/C			4	ID	N/A
	SHELL	SHIELD	BRAID	SHELL	SHIELD	N/A

PART NUMBER	LENGTH METERS [FEET]
CAU2CMICB-03M	0.3 [.98]
CAU2CMICB-05M	0.5 [1.64]
CAU2CMICB-1M	1.0 [3.28]
CAU2CMICB-2M	2.0 [6.56]
CAU2CMICB-3M	3.0 [9.84]
CAU2CMICB-5M	5.0 [16.40]

NOTES:

- CABLE ASSEMBLY SHALL HAVE 360° SHIELD TERMINATION.
- CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
- L-COM LOGO AND USB ICON MAY BE ON ANY SIDE OF THE OVERMOLD FOR USB SERIES "C" END.
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [1.51] .XXX = ± .005 [1.13] PROJECTION 	APPROVALS	DATE	 50 HIGH STREET NORTH ANDOVER, MA 01845
	DRAWN BY D. CASTRO	4/23/15	
	CHECKED BY S. LI	1/15/16	
	APPROVED BY S. LI	1/15/16	
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY			CATEGORY USB
COLOR VARIATIONS MAY OCCUR			PRODUCT DESCRIPTION CBL USB 2.0 TYPE C/MICB
SIZE A	FSCM NO. 43321	DWG. NO. CAU2CMICB	REV. B
SCALE: NONE		CAD FILE: CAU2CMICB.SLDDRW	
		SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[L-Com:](#)

[CAU2CMICB-05M](#) [CAU2CMICB-3M](#) [CAU2CMICB-5M](#) [CAU2CMICB-03M](#) [CAU2CMICB-2M](#) [CAU2CMICB-1M](#)