


SERIES 151 MIL-DTL-55116 QPL Field-Serviceable Audio Plug with wire strain relief







151-001 • M55116/3 - /4 • U-229





Series 151 MIL-DTL-55116 QPL audio plugs are designed for high-reliability, severe environment radio communications equipment. They are available in both 5 pin and 6 pin configurations, with either crimp sleeve (COTS) or solder cup terminals (QPL). All feature versatile wire strain relief to protect cable conductors from damage. Shells are made of nylon overmolded passivated stainless steel, contacts are gold plated copper alloy. Plug connector contacts are sealed in the unmated condition.





U-229 Plug,
5 Crimp Contacts




U-229 Plug,
6 Crimp Contacts



U-229 Plug,
5 Solder Cup
Contacts



U-229 Plug,
6 Solder Cup
Contacts



No. of Contacts	Contact Type	Ø Cable ± .010	MIL SPEC Part Number	Glenair Part Number	Mates With
5	Crimp (COTS)	.165	N/A	151-001-1-1	152-003-1
		.228	N/A	151-001-1-2	152-004-1
		.250	N/A	151-001-1-3	152-004-3
		.290	N/A	151-001-1-4	152-007-5
		.320	N/A	151-001-1-5	151-003-1
6	Crimp (COTS)	.165	N/A	151-001-2-1	151-004-1
		.228	N/A	151-001-2-2	152-003-2
		.250	N/A	151-001-2-3	152-004-2
		.290	N/A	151-001-2-4	152-004-4
		.320	N/A	151-001-2-5	152-007-6
5	Solder Cup (QPL)	.165	M55116/3-1	151-001-3-1	151-003-2
		.228	M55116/3-2	151-001-3-2	151-004-2
		.250	M55116/3-3	151-001-3-3	152-003-1
		.290	M55116/3-4	151-001-3-4	152-004-1
		.320	M55116/3-5	151-001-3-5	152-004-3
6	Solder Cup (QPL)	.165	M55116/4-1	151-001-4-1	151-003-2
		.228	M55116/4-2	151-001-4-2	151-004-2
		.250	M55116/4-3	151-001-4-3	152-003-2
		.290	M55116/4-4	151-001-4-4	152-004-2
		.320	M55116/4-5	151-001-4-5	152-004-4

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Glenair:

[151-001-3-5](#) [151-001-4-4](#) [151-001-4-2](#) [151-001-3-2](#)