



600J005
Plug and Receptacle Holder
MIL-DTL-81511 Series I, II, III & IV



SERIES I and III: Dash Number, Shell Size, Torque and Dimensions

Dash Number	Shell Size Commercial Military Ref	Max Torque (± 5 Inch Lbs)	A Dia Max	B Dia Max	C Dim Max
1A08	08 A	40	.556 (14.1)	.394 (10.0)	.950 (24.1)
1B10	10 B	40	.681 (17.3)	.519 (13.2)	.950 (24.1)
1D14	14 D	40	.931 (23.6)	.769 (19.5)	.950 (24.1)
1E16	16 E	40	1.058 (26.9)	.895 (22.7)	.950 (24.1)
1F18	18 F	40	1.181 (30.0)	1.019 (25.9)	.950 (24.1)
1G20	20 G	40	1.306 (33.2)	1.144 (29.1)	.950 (24.1)
1H22	22 H	40	1.431 (36.3)	1.269 (32.2)	.950 (24.1)
1J24	24 J	40	1.556 (39.5)	1.394 (35.4)	.950 (24.1)

SERIES II and IV: Dash Number, Shell Size, Torque and Dimensions

Dash Number	Shell Size Commercial Military Ref	Max Torque (± 5 Inch Lbs)	A Dia Max	B Dia Max	C Dim Max
2A08	08 A	40	.544 (13.8)	.374 (9.5)	.950 (24.1)
2B10	10 B	40	.669 (17.0)	.499 (12.7)	.950 (24.1)
2D14	14 D	40	.919 (23.3)	.749 (19.0)	.950 (24.1)
2E16	16 E	40	1.045 (26.5)	.875 (22.2)	.950 (24.1)
2F18	18 F	40	1.169 (29.7)	.999 (25.4)	.950 (24.1)

APPLICATION NOTES

1. Metric dimensions (mm) are indicated in parentheses.
2. Material: Case hardened carbon steel with electroless nickel finish.
3. Receptacle and plug holder drives:
1/4" - Shell sizes 08, 10 and 12; 3/8" - Shell sizes 14 and up.

Dimensions in inches (millimeters) and are subject to change without notice.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Glenair:

[600J005-1D14P1](#) [600J005-2E16P1](#) [600J005-1E16P3](#) [600J005-1A08P2](#) [600J005-1E16R2](#) [600J005-1A08P1](#)
[600J005-2F18P2](#)