



M83723/59-2, M83723/60-2, MS27293 and MS29295 Protective Plug and Receptacle Covers Bayonet Coupling

MATING CONNECTOR

MIL-DTL-83723 Bayonet

Superseded Part Number

Basic Part Number
MS27293 = Plug Cover
MS27295 = Receptacle Cover

Dash Number

MS27293 - 1

See Note 3

Basic Part Number

M83723/59-2 = Plug Cover
M83723/60-2 = Receptacle Cover

Shell
Size

Attachment Style

C = 5.0" (127.0) Chain
P = 8.0" (203.2) Chain
R = 5.0" (127.0) Rope
T = 8.0" (203.2) Rope
N = No Attachment

M83723/59-2


10

A


C

Finish

A = Black Anodize
R = Electroless Nickel
W = Cadmium over Electroless Nickel



M83723/59-2 PLUG COVER
M27293 PLUG COVER (SEE NOTE 3)



M83723/60-2 RECEPTACLE COVER

**TABLE I: Shell Size,
Dash Number
and Dimensions**

Shell Size	M27292 M27294 Dash No.	F Dia Max
8	7	.776 (19.7)
10	1	.906 (23.0)
12	2	1.078 (27.4)
14	3	1.141 (29.0)
16	4	1.266 (32.2)
18	5	1.375 (34.9)
20	8	1.510 (38.4)
22	6	1.625 (41.3)
24	9	1.760 (44.7)

Dimensions in inches (millimeters) and are subject to change without notice.

© 2013 Glenair, Inc.

Mil-Spec Backshells

U.S. CAGE Code 06324

Printed in U.S.A.

GLENAIR, INC. • 1211 AIR WAY • GLENDALE, CA 91201-2497 • 818-247-6000 • FAX 818-500-9912
www.glenair.com

E-8
Rev. 10.07.19

E-Mail: sales@glenair.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Glenair:](#)

[MS27293-7](#) [M83723/59-214AR](#) [M83723/60-216AP](#) [M83723/59-214AC](#) [M83723/60-216RR](#) [M83723/60-218AN](#)
[M83723/60-220RC](#) [M83723/59-214WP](#) [M83723/59-222WP](#) [M83723/60-220WP](#) [M83723/59-220RC](#) [M83723/59-](#)
[210RC](#) [M83723/59-210AC](#) [M83723/59-210AN](#) [M83723/59-210AR](#) [M83723/59-210RR](#) [M83723/59-210WC](#)
[M83723/59-210WP](#) [M83723/59-210WR](#) [M83723/59-212AC](#) [M83723/59-212AN](#) [M83723/59-212AR](#) [M83723/59-](#)
[212RN](#) [M83723/59-212RP](#) [M83723/59-212RR](#) [M83723/59-212WN](#) [M83723/59-212WR](#) [M83723/59-212WT](#)
[M83723/59-214AN](#) [M83723/59-214AT](#) [M83723/59-214RC](#) [M83723/59-214RN](#) [M83723/59-214RP](#) [M83723/59-214RR](#)
[M83723/59-214RT](#) [M83723/59-214WN](#) [M83723/59-214WR](#) [M83723/59-216AC](#) [M83723/59-216AN](#) [M83723/59-](#)
[216AR](#) [M83723/59-216RC](#) [M83723/59-216RN](#) [M83723/59-216RP](#) [M83723/59-216WC](#) [M83723/59-216WP](#)
[M83723/59-218AN](#) [M83723/59-218AR](#) [M83723/59-218RC](#) [M83723/59-218RP](#) [M83723/59-218RR](#) [M83723/59-218RT](#)
[M83723/59-218WC](#) [M83723/59-220AN](#) [M83723/59-220AP](#) [M83723/59-220AR](#) [M83723/59-220AT](#) [M83723/59-](#)
[220RN](#) [M83723/59-220RP](#) [M83723/59-220RT](#) [M83723/59-220WR](#) [M83723/59-222AC](#) [M83723/59-222AN](#)
[M83723/59-222AR](#) [M83723/59-222AT](#) [M83723/59-222RC](#) [M83723/59-222RN](#) [M83723/59-222RR](#) [M83723/59-](#)
[222WC](#) [M83723/59-222WR](#) [M83723/59-222WT](#) [M83723/59-224AC](#) [M83723/59-224AR](#) [M83723/59-224AT](#)
[M83723/59-224RC](#) [M83723/59-224RP](#) [M83723/59-224RR](#) [M83723/59-224RT](#) [M83723/59-224WC](#) [M83723/59-](#)
[224WP](#) [M83723/59-224WR](#) [M83723/59-28AC](#) [M83723/59-28AN](#) [M83723/59-28AR](#) [M83723/59-28RC](#) [M83723/59-](#)
[28RR](#) [M83723/59-28WP](#) [M83723/60-210RC](#) [M83723/60-210RN](#) [M83723/60-210RR](#) [M83723/60-210WC](#) [M83723/60-](#)
[210WN](#) [M83723/60-210WR](#) [M83723/60-212AR](#) [M83723/60-212RN](#) [M83723/60-212RR](#) [M83723/60-212WN](#)
[M83723/60-212WP](#) [M83723/60-212WR](#) [M83723/60-214AP](#) [M83723/60-214AT](#)