





MS27475

Wall Mount Hermetic Receptacle

MIL-DTL-38999 Series II

How To Order: MS

B



Dimensions in Inches (millimeters) are subject to change without notice.

232-100-H0


Wall Mount Hermetic Receptacle

MIL-DTL-38999 Series II Type



MIL-DTL-38999 Type
Hermetic Connectors

How To Order: Commercial



B

TABLE I: CONNECTOR DIMENSIONS


SHELL SIZE	A BSC	B SQ MAX	ø C HOLES	D Threads (UNEF-2A)	ø E MAX	FP MAX	FS MAX
8/08	.594(15.1)	.828(21.0)	.130(3.3) .115(2.9)	.5625-24	1.078(27.4)	.250 (6.35)	.375 (9.5)
10	.719(18.3)	.954(24.2)		.6875-24	1.256(31.9)		
12	.812(20.6)	1.047(26.6)		.8125-20	1.391(35.3)		
14	.906(23.0)	1.141(29.0)		.9375-20	1.516(38.5)		
16	.969(24.6)	1.234(31.3)		1.0625-18	1.641(41.7)		
18	1.062(27.0)	1.328(33.7)		1.1875-18	1.766(44.9)		
20	1.156(29.4)	1.453(36.9)		1.3125-18	1.891(48.0)		
22	1.250(31.8)	1.578(40.1)	.157(4.0) .142(3.6)	1.4375-18	2.016(51.2)	.375 (9.53)	.406 (10.3)
24	1.375(34.9)	1.703(43.3)		1.5625-18	2.204(56.0)		

TABLE I (CONTINUED):
CONNECTOR DIMENSIONS

SHELL SIZE	ø G HOLES	ø H MIN	ø J BSC
8	.133(3.4) .123(3.1)	.570(14.5)	.594(15.1)
10		.690(17.5)	.719(18.3)
12		.820(20.8)	.812(20.6)
14		.940(23.9)	.906(23.0)
16		1.070(27.2)	.969(24.6)
18		1.190(30.2)	1.062(27.0)
20	.159(4.0) .149(3.8)	1.320(33.5)	1.156(29.4)
22		1.440(36.6)	1.250(31.8)
24		1.570(39.9)	1.375(34.9)

TABLE II: CONTACT SIZE

PRINTED CIRCUIT TAIL
CONFIGURATIONS
CONTACT STYLE C AND D



Contact Size	ø P
22D	.011 (0.28) .015 (0.38)
20	.024 (0.61) .028 (0.71)
16	.0635 (1.61) .0615 (1.56)
12	.095 (2.41) .093 (2.36)

WIRE ACCOMODATION

Contact Size	Wire Gauge
22D	#22 - #28
20	#20 - #24
16	#16 - #20
12	#12 - #14

HERMETIC LEAK RATE MOD CODES

Designator	Required Leak Rate
-585A	1 x 10 ⁻¹⁰ cc Helium per second
-585B	1 x 10 ⁻⁹ cc Helium per second
-585C	1 x 10 ⁻⁸ cc Helium per second

Dimensions in Inches (millimeters) are subject to change without notice.

© 2013 Glenair, Inc.

U.S. CAGE Code 06324

Printed in U.S.A.

GLENAIR, INC. • 1211 AIR WAY • GLENDALE, CA 91201-2497 • 818-247-6000 • FAX 818-500-9912
www.glenair.com B-31 E-Mail: sales@glenair.com

Rev 02/22/2022

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Glenair:

[232-100-H0ZL1005PB](#) [232-100-H0ZL1005PA](#) [232-100-H0ZL14-35CN](#) [232-100-H2FT10-05PN](#) [232-100-H2Z110-99PN](#) [232-100-H2Z112-98SN](#) [232-100-H2ZL12-35PA](#) [232-100-H2ZL24-35CA](#) [232-100-H2ZL24-35DA](#) [232-100-H7ZL16-35CB](#) [232-100-H7ZL16-35CN](#) [232-100-H5Z116-26PN](#) [232-100-H7Z112-35SN](#) [232-100-H7Z116-26PN](#) [232-100-H7ZL14-35CN](#) [232-100-H7ZL14-35SN](#) [232-100-H7ZL16-35CA](#)