

ESSENTIAL ELECTRICAL KITS

TK-30A • TK-30AGFI



MULTIMETER

Measure AC/DC voltage up to 600V



NON-CONTACT VOLTAGE DETECTOR

Safely detect AC Voltage



RECEPTACLE TESTER

Ensure sockets are wired correctly and test Ground Fault Circuit Interrupter (GFCI) device for proper operation.*



TK-30A

Kit includes:

- Multimeter (DM-25)
- Non-contact Voltage Detector (GT-11)
- Receptacle Tester (GT-10)
- Carrying Case



TK-30AGFI

Kit includes:

- Multimeter (DM-25)
- Non-contact Voltage Detector (GT-11)
- Receptacle Tester (GT-10GFI)
- Carrying Case

All the features of TK-30A PLUS
Ground-Fault Circuit Interrupter (GFCI) Testing



GREENLEE®
A Textron Company

USA PHONE 800.435.0786
FAX 800.451.2632

CANADA PHONE 866.384.8813
FAX 800.524.2853

INT'L PHONE +1.815.397.7070
FAX +1.815.397.9247

* GFCI testing available with TK-30AGFI Kit.

TK-30A • TK-30AGFI

ESSENTIAL ELECTRICAL KITS

FOR PRODUCT VIDEOS, DEMONSTRATIONS
AND MORE, SCAN THIS QR CODE OR VISIT:
www.youtube.com/GreenleeDEMO



	DM-25	GT-11	GT-10 / GT-10GFI
FASTER	Large, easy to read display	Bright LED and audible alarm quickly warns user of live voltage	Instant results – quickly detect correct wiring
SAFER	CAT III 600 V rated	Non-contact design reduces risk of shock	No need to remove sockets – simply plug in
EASIER	Test leads attached – no loose parts	Small design fits in pockets for quick access	Lights indicate correct/incorrect wiring. Results chart printed on unit.



SPECIFICATIONS

Voltage measurement	600 V AC/DC	Voltage Detection	50 V to 1,000 V AC	Maximum Voltage	125 V AC
Resistance measurement	2 MΩ	Frequency	50-500 Hz	Approval	ETL
Battery Test	1.5 V, 9 V	Measurement Category	CAT IV 1,000 V		
Measurement Category	CAT III 600 V	Approval	ETL, CE		
Approval	ETL, CE				

ORDERING INFORMATION

CAT. NO.	UPC NO.	DESCRIPTION
TK-30A	00880	Basic Electrical Kit (includes: DM-25, GT-11, GT-10)
TK-30AGFI	01575	GFCI Electrical Kit (includes: DM-25, GT-11, GT-10GFI)
AVAILABLE SEPARATELY		
DM-25	00334	Digital Multimeter, CAT III 600V
GT-10	12124	Receptacle Tester
GT-10GFI	12125	Receptacle Tester, GFCI



www.greenlee.com MA6049 09/13
4455 Boeing Drive • Rockford, IL 61109-2988 • USA • 815-397-7070
©2013 Greenlee Textron Inc. • An ISO 9001 Company • Printed in USA
Greenlee Textron Inc. is a subsidiary of Textron Inc.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Greenlee:](#)

[TK-30A](#) [TK-30AGFI](#)