




Quality Products. Service Excellence.

Type 3R Louvered Vent Kits 1481L3R Series



Features

- Provides ventilation in enclosures for either indoor or outdoor locations
- Gasketed sealing kit provides protection to NEMA 3R
- Aluminum filter mesh provides ingress protection for both solid debris and outdoor rain conditions
- Field installation kit includes all hardware
- Louver plates are offered in both 14 gauge steel with ANSI61 Gray power coat finish or 304 Stainless Steel
- Kits are sold in QTY 1. Replacement filter kits are sold in QTY 2.



Part Number		Overall Size H x W (inches)	Number of Louvers	Louver Length (inches)
ANSI 61 Gray	Stainless Steel			
1481L3R55GY	1481L3R55SS	5.56 x 5.30	3	3.00
1481L3R56GY	1481L3R56SS	5.30 x 6.30	3	4.00
1481L3R66GY	1481L3R66SS	6.40 x 6.30	4	4.00
1481L3R68GY	-	6.40 x 8.30	10	2.00
1481L3R88GY	-	8.69 x 8.30	16	2.00
1481L3R610GY	-	6.62 x 10.30	10	3.00
1481L3R810GY	-	9.0 x 10.30	14	3.00
1481L3R1110GY	-	11.37 x 10.30	20	3.00
1481L3R1510GY	-	16.12 x 10.30	34	3.00

Replacement Aluminum Filters

Part Number	Size H x W (in)
LFK55	3.50 x 3.00
LFK56	3.375 x 4.00
LFK66	4.375 x 4.00
LFK68	4.375 x 6.00
LFK88	6.625 x 6.00
LFK610	4.563 x 8.00
LFK810	6.398 x 8.00
LFK1110	9.313 x 8.00
LFK1510	14.063 x 8.00

Tags: Type 3R, outdoor, indoor, louver, louvered, rain, debris, ingress, ventilation, stainless, filter

Data subject to change without notice

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hammond:](#)

[1481L3R55SS](#) [1481L3R810GY](#) [1481L3R610GY](#) [1481L3R66SS](#) [1481L3R56GY](#) [1481L3R68GY](#) [1481L3R66GY](#)
[1481L3R55GY](#) [1481L3R1510GY](#) [1481L3R56SS](#) [LFK68](#) [LFK810](#) [LFK1510](#) [LFK55](#) [LFK66](#) [LFK610](#) [LFK56](#)
[LFK1110](#) [1481L3R88GY](#) [1481L3R1110GY](#) [LFK88](#)