



Quality Products. Service Excellence.

20° Rack Consoles 1564 Series

Load rated to 600 lbs (272 kg)



Features

- Constructed in 14-gauge steel (frame) and 14-gauge steel (rails).
- Choice of two depths, 24.5", and 31.5" usable depth.
- 20° Sloped panel height of 17.5" (10 U).
- Front panel height of 26.25" (15U).
- Finished in textured RAL9005 black powder paint. Complies with the Greenguard guidelines for indoor air quality.
- 600 lbs (272 kg) **static load rating**.
- TAA-compliant for GSA Schedule purchases. BAA/TAA-compliant documentation available upon request.
- RoHS Compliant.
- Manufactured in North America within an ISO 9001:2015 certified facility.



Unit is Shipped Complete with

- Two (2) pairs of EIA-compliant pre-installed upper and lower round hole-punched **combination rails**.
 - Starter pack of **1421N25** clip nuts
- One (1) Set of four (4) leveling feet




AVAILABLE
BY SPECIAL
ORDER



Accessories

- Rack Shelves
- Rack Panels
- Equipment Cooling
- Rack Mount Desk
- PDUs and Outlet Strips
- Cable Managers
- Hardware for Rack Mounting Solutions



1564 Frame and Side Panels

Part No.	Overall Dimensions			Mounting			Top (D) Fixed Rack Units	Mounting Dimensions		
	Height	Width (A)	Depth (B)	Width (C)	E	F		Upper Front Rack Units	Lower Front Rack Units	Rear Fixed Rack Units
1564A2BK1	49.89	22.56	24.50	19.06	17.50	21.31	8U	10U	15U	24U
1564B2BK1	49.89	22.56	31.50	19.06	24.50	19.56	12U	10U	15U	24U

Side Panels Sold in Pairs

1564 Doors

Door Type	Part No. Front Door	Part No. Rear Door
Solid	RSDF19026BK1	RSDF19042BK1
Louvered	RSDL19026BK1	RSDL19042BK1

Doors are constructed of 18 gauge steel and feature lockable latch.

1564 Top Panels

For Use With Frame	Rack Units	Part No. Solid Panel	Part No. Vented Steel Panel	Part No. Raised Solid Panel	Part No. Solid Side Panel (Pair)
1564A2BK1	8U	PBPS19014BK2	Qty 2 x PPFS19007BK2	PBRS19014BK2	1564APBK1
1564B2BK1	12U	PBPS19021BK2	Qty 2 x PPFS19010BK2	PBRS19021BK2	1564BPBK1

1564 Corner Wedges

Part No.	For Use With Frame
1564AW30BK1	1564A2
1564BW30BK1	1564B2
1564AW60BK1	1564A2
1564BW60BK1	1564B2

1564 Rack Rails

Part No.	Mounting Dimensions	
	Rack Units	Height
RSRC00017BK3	10U	17.00
RSRC00026BK3	15U	26.00

Data subject to change without notice

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hammond:](#)

[RSDF19042CG1](#) [RSDL19042CG1](#) [1564APCG1](#) [RSDL19026CG1](#) [1564APBK1](#) [1564A2CG1](#) [1564BW60BK1](#)
[1564AW60BK1](#) [1564BW30CG1](#) [1564AW30CG1](#) [RSDF19022BK1](#) [RSDF19026CG1](#) [1564BPCG1](#) [RSDF19026BK1](#)
[PVLK19014CG1](#) [1564A2BK1](#) [1564BPBK1](#) [PVLK19021CG1](#) [1564BW60CG1](#) [1564AW60CG1](#) [1564B2CG1](#)
[1564B2BK1](#) [RSDL19026BK1](#) [1564BW30BK1](#) [1564AW30BK1](#) [RSRC00017BK3](#) [PBRs19021CG2](#) [PBRs19021BK2](#)
[PBRs19014CG2](#) [PBRs19014BK2](#) [RSRC00026BK3](#)