




*Quality Products. Service Excellence.*

## Vertical Basic PDU 1585-6-7-8 Series

15A | 120V Single-Phase | 5-15R Outlets



### Features

- Low-profile slim design constructed of rugged lightweight aluminum.
- It can also be used horizontally on your workbench.
- Each outlet strip includes a hardware mounting kit. Order P/N: **1585CLIP** for additional hardware kit.
- Receptacles are 1" square and are equally spaced over the length of the power strip.
- Available with a rocker switch or power indicator light and 15 Amp circuit breaker.

### Specifications

- Heavy duty 14 gauge wire cord - 14/3 SJT type for extreme temperature ranges and integral moulded plug.
- Plug types available are NEMA 5-15P straight blade or NEMA L5-15P locking type.
- Rated 15 amps, 120 volts.
- UL/cUL Listed Standard UL1363, CSA C22.2 No. 308-14 and CSA C22.2 No. 0.4-04
- TAA-compliant for GSA Schedule purchases.
- RoHS Compliant.
- Manufactured in North America.

### Surge Specifications

- Max Energy (Joules) is 1080 J.
- 25000 Amp-rated MOV's for 75,000 Amps of single pulse transient current.
- Voltage Protection Rating (Vpr) of 500V in all three modes (L-N, L-G, N-G).
- Nominal Discharge Current (In) of 5kA.
- Voltage suppression at the outlet guards against transients from the equipment on the outlet strip.
- The green indicator light confirms surge module is active.
- Internal protection will disconnect the surge module at the end of its useful life (and extinguish the green light) but will maintain power to the load, now unprotected.
- cULus Listed to UL 1449 & C22.2 No. 269.3-17, for Surge Protective Devices – Type 3.
- cULus Listed to UL 1363 & C22.2 No. 308-18, for Relocatable Power Taps & Multi Outlet

### Plug Types



5-15P Straight Blade

L5-15P Locking Type

### Accessories

- Vertical Outlet Strip Mounting Clip Kit

| Part No.<br>On-Off Switch | Part No.<br>Pilot Light | Strip<br>Length | Number<br>of Outlets | Cord<br>Length (ft) | Color   | NEMA<br>Plug Type | Surge<br>Protected |
|---------------------------|-------------------------|-----------------|----------------------|---------------------|---------|-------------------|--------------------|
| 15851H6A1                 | 15851T6A1               | 18.00           | 6                    | 6                   | Natural | 5-15P             | No                 |
| 15851H6C1                 | 15851T6C1               | 18.00           | 6                    | 6                   | Natural | L5-15P            | No                 |
| 15851H6B1                 | 15851T6B1               | 18.00           | 6                    | 15                  | Natural | 5-15P             | No                 |
| 15851H6D1                 | 15851T6D1               | 18.00           | 6                    | 15                  | Natural | L5-15P            | No                 |
| 15852H6A1                 | 15852T6A1               | 24.00           | 6                    | 6                   | Natural | 5-15P             | No                 |
| 15852H6C1                 | 15852T6C1               | 24.00           | 6                    | 6                   | Natural | L5-15P            | No                 |
| 15852H6B1                 | 15852T6B1               | 24.00           | 6                    | 15                  | Natural | 5-15P             | No                 |
| 15852H6D1                 | 15852T6D1               | 24.00           | 6                    | 15                  | Natural | L5-15P            | No                 |
| 15852H8A1                 | 15852T8A1               | 24.00           | 8                    | 6                   | Natural | 5-15P             | No                 |
| 15852H8C1                 | 15852T8C1               | 24.00           | 8                    | 6                   | Natural | L5-15P            | No                 |
| 15852H8B1                 | 15852T8B1               | 24.00           | 8                    | 15                  | Natural | 5-15P             | No                 |
| 15852H8D1                 | 15852T8D1               | 24.00           | 8                    | 15                  | Natural | L5-15P            | No                 |
| 15853H6A1                 | 15853T6A1               | 36.00           | 6                    | 6                   | Natural | 5-15P             | No                 |
| 15853H6C1                 | 15853T6C1               | 36.00           | 6                    | 6                   | Natural | L5-15P            | No                 |
| 15853H6B1                 | 15853T6B1               | 36.00           | 6                    | 15                  | Natural | 5-15P             | No                 |
| 15853H6D1                 | 15853T6D1               | 36.00           | 6                    | 15                  | Natural | L5-15P            | No                 |
| 15853H12A1                | 15853T12A1              | 36.00           | 12                   | 6                   | Natural | 5-15P             | No                 |
| 15854H7A1                 | 15854T7A1               | 42.00           | 7                    | 6                   | Natural | 5-15P             | No                 |
| 15854H7C1                 | 15854T7C1               | 42.00           | 7                    | 6                   | Natural | L5-15P            | No                 |
| 15854H7B1                 | 15854T7B1               | 42.00           | 7                    | 15                  | Natural | 5-15P             | No                 |
| 15854H7D1                 | 15854T7D1               | 42.00           | 7                    | 15                  | Natural | L5-15P            | No                 |
| 1585H8A1                  | 1585T8A1                | 48.00           | 8                    | 6                   | Natural | 5-15P             | No                 |
| 1585H8A1BK                | 1585T8A1BK              | 48.00           | 8                    | 6                   | Black   | 5-15P             | No                 |
| 1585H8A1S                 | 1585T8A1S               | 48.00           | 8                    | 6                   | Natural | 5-15P             | Yes                |
| 1585H8C1                  | 1585T8C1                | 48.00           | 8                    | 6                   | Natural | L5-15P            | No                 |
| 1585H8B1                  | 1585T8B1                | 48.00           | 8                    | 15                  | Natural | 5-15P             | No                 |
| 1585H8B1BK                | 1585T8B1BK              | 48.00           | 8                    | 15                  | Black   | 5-15P             | No                 |
| 1585H8B1S                 | 1585T8B1S               | 48.00           | 8                    | 15                  | Natural | 5-15P             | Yes                |
| 1585H8D1                  | 1585T8D1                | 48.00           | 8                    | 15                  | Natural | L5-15P            | No                 |
| 1585H10A1                 | 1585T10A1               | 48.00           | 10                   | 6                   | Natural | 5-15P             | No                 |
| 1585H10A1S                | 1585T10A1S              | 48.00           | 10                   | 6                   | Natural | 5-15P             | Yes                |
| 1585H10C1                 | 1585T10C1               | 48.00           | 10                   | 6                   | Natural | L5-15P            | No                 |
| 1585H10B1                 | 1585T10B1               | 48.00           | 10                   | 15                  | Natural | 5-15P             | No                 |
| 1585H10B1S                | 1585T10B1S              | 48.00           | 10                   | 15                  | Natural | 5-15P             | Yes                |
| 1585H10D1                 | 1585T10D1               | 48.00           | 10                   | 15                  | Natural | L5-15P            | No                 |
| 1585H11A1                 | 1585T11A1               | 48.00           | 11                   | 6                   | Natural | 5-15P             | No                 |
| 1585H11C1                 | 1585T11C1               | 48.00           | 11                   | 6                   | Natural | L5-15P            | No                 |
| 1585H11B1                 | 1585T11B1               | 48.00           | 11                   | 15                  | Natural | 5-15P             | No                 |
| 1585H11D1                 | 1585T11D1               | 48.00           | 11                   | 15                  | Natural | L5-15P            | No                 |
| 1585H15A1                 | 1585T15A1               | 48.00           | 15                   | 6                   | Natural | 5-15P             | No                 |
| 1585H15A1S                | 1585T15A1S              | 48.00           | 15                   | 6                   | Natural | 5-15P             | Yes                |
| 1585H15C1                 | 1585T15C1               | 48.00           | 15                   | 6                   | Natural | L5-15P            | No                 |
| 1585H15B1                 | 1585T15B1               | 48.00           | 15                   | 15                  | Natural | 5-15P             | No                 |
| 1585H15B1S                | 1585T15B1S              | 48.00           | 15                   | 15                  | Natural | 5-15P             | Yes                |
| 1585H15D1                 | 1585T15D1               | 48.00           | 15                   | 15                  | Natural | L5-15P            | No                 |
| 1585H16A1                 | 1585T16A1               | 48.00           | 16                   | 6                   | Natural | 5-15P             | No                 |
| 1585H16C1                 | 1585T16C1               | 48.00           | 16                   | 6                   | Natural | L5-15P            | No                 |
| 1585H16B1                 | 1585T16B1               | 48.00           | 16                   | 15                  | Natural | 5-15P             | No                 |
| 1585H16D1                 | 1585T16D1               | 48.00           | 16                   | 15                  | Natural | L5-15P            | No                 |
| 1586H10A1                 | 1586T10A1               | 60.00           | 10                   | 6                   | Natural | 5-15P             | No                 |
| 1586H10C1                 | 1586T10C1               | 60.00           | 10                   | 6                   | Natural | L5-15P            | No                 |

| Part No.<br>On-Off Switch | Part No.<br>Pilot Light | Strip<br>Length | Number<br>of Outlets | Cord<br>Length (ft) | Color   | NEMA<br>Plug Type | Surge<br>Protected |
|---------------------------|-------------------------|-----------------|----------------------|---------------------|---------|-------------------|--------------------|
| 1586H10B1                 | 1586T10B1               | 60.00           | 10                   | 15                  | Natural | 5-15P             | No                 |
| 1586H10D1                 | 1586T10D1               | 60.00           | 10                   | 15                  | Natural | L5-15P            | No                 |
| 1586H12A1                 | 1586T12A1               | 60.00           | 12                   | 6                   | Natural | 5-15P             | No                 |
| 1586H12A1BK               | 1586T12A1BK             | 60.00           | 12                   | 6                   | Black   | 5-15P             | No                 |
| 1586H12C1                 | 1586T12C1               | 60.00           | 12                   | 6                   | Natural | L5-15P            | No                 |
| 1586H12B1                 | 1586T12B1               | 60.00           | 12                   | 15                  | Natural | 5-15P             | No                 |
| 1586H12B1BK               | 1586T12B1BK             | 60.00           | 12                   | 15                  | Black   | 5-15P             | No                 |
| 1586H12D1                 | 1586T12D1               | 60.00           | 12                   | 15                  | Natural | L5-15P            | No                 |
| 1586H20A1                 | 1586T20A1               | 60.00           | 20                   | 6                   | Natural | 5-15P             | No                 |
| 1587H10A1                 | 1587T10A1               | 70.00           | 10                   | 6                   | Natural | 5-15P             | No                 |
| 1587H10A1BK               | 1587T10A1BK             | 70.00           | 10                   | 6                   | Black   | 5-15P             | No                 |
| 1587H10C1                 | 1587T10C1               | 70.00           | 10                   | 6                   | Natural | L5-15P            | No                 |
| 1587H10B1                 | 1587T10B1               | 70.00           | 10                   | 15                  | Natural | 5-15P             | No                 |
| 1587H10B1BK               | 1587T10B1BK             | 70.00           | 10                   | 15                  | Black   | 5-15P             | No                 |
| 1587H10D1                 | 1587T10D1               | 70.00           | 10                   | 15                  | Natural | L5-15P            | No                 |
| 1587H11A1                 | 1587T11A1               | 70.00           | 11                   | 6                   | Natural | 5-15P             | No                 |
| 1587H11A1S                | 1587T11A1S              | 70.00           | 11                   | 6                   | Natural | 5-15P             | Yes                |
| 1587H11C1                 | 1587T11C1               | 70.00           | 11                   | 6                   | Natural | L5-15P            | No                 |
| 1587H11B1                 | 1587T11B1               | 70.00           | 11                   | 15                  | Natural | 5-15P             | No                 |
| 1587H11B1S                | 1587T11B1S              | 70.00           | 11                   | 15                  | Natural | 5-15P             | Yes                |
| 1587H11D1                 | 1587T11D1               | 70.00           | 11                   | 15                  | Natural | L5-15P            | No                 |
| 1587H12A1                 | 1587T12A1               | 70.00           | 12                   | 6                   | Natural | 5-15P             | No                 |
| 1587H12C1                 | 1587T12C1               | 70.00           | 12                   | 6                   | Natural | L5-15P            | No                 |
| 1587H12B1                 | 1587T12B1               | 70.00           | 12                   | 15                  | Natural | 5-15P             | No                 |
| 1587H12D1                 | 1587T12D1               | 70.00           | 12                   | 15                  | Natural | L5-15P            | No                 |
| 1587H19A1                 | 1587T19A1               | 70.00           | 19                   | 6                   | Natural | 5-15P             | No                 |
| 1587H19A1S                | 1587T19A1S              | 70.00           | 19                   | 6                   | Natural | 5-15P             | Yes                |
| 1587H19C1                 | 1587T19C1               | 70.00           | 19                   | 6                   | Natural | L5-15P            | No                 |
| 1587H19B1                 | 1587T19B1               | 70.00           | 19                   | 15                  | Natural | 5-15P             | No                 |
| 1587H19B1S                | 1587T19B1S              | 70.00           | 19                   | 15                  | Natural | 5-15P             | Yes                |
| 1587H19D1                 | 1587T19D1               | 70.00           | 19                   | 15                  | Natural | L5-15P            | No                 |
| 1587H24A1                 | 1587T24A1               | 70.00           | 24                   | 6                   | Natural | 5-15P             | No                 |
| 1587H24C1                 | 1587T24C1               | 70.00           | 24                   | 6                   | Natural | L5-15P            | No                 |
| 1587H24B1                 | 1587T24B1               | 70.00           | 24                   | 15                  | Natural | 5-15P             | No                 |
| 1587H24D1                 | 1587T24D1               | 70.00           | 24                   | 15                  | Natural | L5-15P            | No                 |
| 1588H12A1                 | 1588T12A1               | 77.00           | 12                   | 6                   | Natural | 5-15P             | No                 |
| 1588H12A1BK               | 1588T12A1BK             | 77.00           | 12                   | 6                   | Black   | 5-15P             | No                 |
| 1588H12A1S                | 1588T12A1S              | 77.00           | 12                   | 6                   | Natural | 5-15P             | Yes                |
| 1588H12C1                 | 1588T12C1               | 77.00           | 12                   | 6                   | Natural | L5-15P            | No                 |
| 1588H12B1                 | 1588T12B1               | 77.00           | 12                   | 15                  | Natural | 5-15P             | No                 |
| 1588H12B1BK               | 1588T12B1BK             | 77.00           | 12                   | 15                  | Black   | 5-15P             | No                 |
| 1588H12B1S                | 1588T12B1S              | 77.00           | 12                   | 15                  | Natural | 5-15P             | Yes                |
| 1588H12D1                 | 1588T12D1               | 77.00           | 12                   | 15                  | Natural | L5-15P            | No                 |

Data subject to change without notice

© 2025. Hammond Manufacturing Ltd. All rights reserved.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hammond:](#)

[1588T12D1BK](#)