

Solid Top Panel C2TS Series

Features



- Use with **C2, C2RR, C4, C4RR, H1, RCK** or **CLC** cabinet series.
  - H1 requires H1TC Series for mounting.
- 14 gauge steel construction.
- Encloses cabinets for airflow management.
- **CLPKIT832-6** Cabinet mounting hardware included.
- Finished in RAL9005 black or ASA61 gray powder paint coat.
  - Complies with the Greenguard guidelines for indoor air quality.
- TAA-compliant for GSA Schedule purchases.
- RoHS and REACH compliant.
- Manufactured in North America.

| Part No.<br>Black | Part No.<br>Light Gray | Overall Dimesnsions |       |
|-------------------|------------------------|---------------------|-------|
|                   |                        | Width               | Depth |
| C2T1923SBK1       | C2T1923SLG1            | 20.00               | 15.00 |
| C2T1931SBK1       | C2T1931SLG1            | 20.00               | 23.75 |
| C2T1936SBK1       | C2T1936SLG1            | 20.00               | 28.25 |
| C2T2423SBK1       | C2T2423SLG1            | 25.00               | 15.00 |
| C2T2431SBK1       | C2T2431SLG1            | 25.00               | 23.75 |
| C2T2436SBK1       | C2T2436SLG1            | 25.00               | 28.25 |

Cabinet Compatibility

| Fan Top<br>Size | C2 Cabinet |       | C4 Cabinet |       | DCZ4 Cabinet |       | H1        | RCK       |
|-----------------|------------|-------|------------|-------|--------------|-------|-----------|-----------|
|                 | Width      | Depth | Width      | Depth | Width        | Depth | Cabinet   | Cabinet   |
| C2T1923*        | 23.00      | 23.63 | 24.00      | 31.50 | -            | -     | All Sizes | All Sizes |
| C2T1931*        | 23.00      | 31.50 | 24.00      | 36.00 | -            | -     | -         | -         |
| C2T1936*        | 23.00      | 36.00 | 24.00      | 42.00 | -            | -     | -         | -         |
| C2T2423*        | -          | -     | 30.00      | 31.50 | -            | -     | -         | -         |
| C2T2431*        | -          | -     | 30.00      | 36.00 | 30.00        | 42.00 | -         | -         |
| C2T2436*        | -          | -     | 30.00      | 42.00 | -            | -     | -         | -         |

What's Inside the Box

| Qty Included | Description                             | Replacement Part No. |
|--------------|-----------------------------------------|----------------------|
| 1            | Top Panel                               |                      |
| 6            | 8-32 Clip Nut (Black Oxide Finish)      | CLPKIT832-6          |
| 6            | 8-32 x 0.5" Machine Screw (Zinc Plated) | CLPKIT832-6          |

Data subject to change without notice

© 2024. Hammond Manufacturing Ltd. All rights reserved.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hammond:](#)

[C2T1931SBK1](#) [C2T1936SBK1](#) [C2T1923SBK1](#) [C2T2431SBK1](#) [C2T1931SLG1](#) [C2T1923SLG1](#) [C2T1936SLG1](#)  
[C2T2431SLG1](#) [C2T2423SBK1](#) [C2T2436SBK1](#) [C2T2423SLG1](#) [C2T2436SLG1](#)