



Quality Products. Service Excellence.

Type 4X Stainless Steel Junction Box C4XSC Series

Heavy Duty Screw Cover

NEW



Application

- Designed for use as a wiring box, junction box, terminal or pull box in indoor or outdoor applications where subject to hose down/precipitation or corrosion.

Standards

- UL 508A Listed; Type 3, 4X, 12
- cULus Listed per CSA C22.2 No 94; Type 3, 4X, 12
- Complies with
 - NEMA Type 3, 4X and 12
 - IEC 60529, IP66

Construction

- 14 gauge 304 stainless steel body up to 24"x24"; 12 gauge body when 30"x30" or larger
- 14 gauge 304 stainless steel cover up to 24"x24"; 12 gauge cover when 30"x30" or larger
- Smooth, continuously welded seams without knockouts, cutouts, or holes
- Captivated stainless steel cover screws thread into sealed wells
- Seamless poured-in place gasket
- No provision for inner mounting panel
- Mounting Foot Kit sold separately - use **C4XMTGFOOT**
- Replacement lid cover screws (package of 25) - use **1421A4XLCS25SS**
- Replacement lid cover washers/sealed wells (package of 25) - use **1421A4XLCW25**

Finish

- Enclosure and cover are unpainted, with a grained #4 finish.

Part No.	Enclosure		
	H	W	D
C4XSC664SS	6.00	6.00	4.00
C4XSC666SS	6.00	6.00	6.00
C4XSC864SS	8.00	6.00	4.00
C4XSC884SS	8.00	8.00	4.00
C4XSC886SS	8.00	8.00	6.00
C4XSC1084SS	10.00	8.00	4.00
C4XSC10104SS	10.00	10.00	4.00
C4XSC10106SS	10.00	10.00	6.00
C4XSC12124SS	12.00	12.00	4.00
C4XSC12126SS	12.00	12.00	6.00
C4XSC12128SS	12.00	12.00	8.00
C4XSC16166SS	16.00	16.00	6.00
C4XSC16168SS	16.00	16.00	8.00
C4XSC18186SS	18.00	18.00	6.00
C4XSC24246SS	24.00	24.00	6.00
C4XSC24248SS	24.00	24.00	8.00
C4XSC242410SS	24.00	24.00	10.00
C4XSC242412SS	24.00	24.00	12.00

Part No.	Enclosure		
	H	W	D
C4XSC303012SS	30.00	30.00	12.00
C4XSC363612SS	36.00	36.00	12.00

Tags: **Type 4X, NEMA 4X, junction box, wiring box, outdoor, indoor, stainless steel, corrosion**

Data subject to change without notice

© 2025. Hammond Manufacturing Ltd. All rights reserved.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hammond:](#)

[C4XSC664SS](#)