



Quality Products. Service Excellence.

2-Post Open Frame Rack *DNRRLDK Series*

Load rated to 800 lbs (363 kg)



When strength and reliability are the highest priority, be sure to choose the Data/Networking Robust Rack (DNRR) from Hammond Manufacturing. Designed to support your rack-mount infrastructure, regardless of the application, the DNRR includes premium features not found on most other racks.

Features:

- Constructed in 12-gauge steel.
- Our automated tapping process provides EIA-compliant 10-32 tapped rails **on the front** to ensure ease of mounting rack-mount equipment.
 - Includes marked rack unit dividers to aid in equipment mounting.
 - Don't forget to order your **Mounting Hardware**.
- To keep the rack upright when it is loaded with equipment, we've included a large base for freestanding support. Optionally, the base can be caster mounted when you need to move your rack.
- To keep it looking great, the DNRR undergoes a three-stage paint process which includes a coat of premium smooth black powder paint. Complies with the Greenguard guidelines for indoor air quality.
- Self-squaring design ships un-assembled (some assembly required).
- 800 lbs (363 kg) **static load rating**.
- TAA-compliant for GSA Schedule purchases.
 - BAA/TAA-compliant documentation available upon request.
- RoHS Compliant.
- Manufactured in North America within an ISO 9001:2015 certified facility.

Gallery



Accessories

- | | |
|--|--|
| <ul style="list-style-type: none"> • Cable Managers • Hinged Clear Security Cover • Adjustable Rack Shelf • Keyboard & Equipment Rack Shelf • Adjustable Rack Mount DIN Rail Kit • Open Frame Rack and Rack Cabinet Joining Kit • Bonding and Grounding • PDUs and Outlet Strips | <ul style="list-style-type: none"> • Rack Panels • Universal Rack Shelf • Centered Rack Shelf • Clamping Rack Shelf • Rack Unit Label • Rack and Cabinet Caster Set • 10-32 Mounting Hardware |
|--|--|

Part No.	Overall Dimensions			Rack	Mounting Dimensions	
	Height	Width	Depth	Units	Height	Width
DNRR1942LDK	45.00	20.00	19.81	24U	42.00	19.00
DNRR1963LDK	66.00	20.00	19.81	36U	63.00	19.00
DNRR1970LDK	73.00	20.00	19.81	40U	70.00	19.00
DNRR1977LDK	80.00	20.00	19.81	44U	77.00	19.00

What's in the Box

Qty Included	Description	Replacement Part No.
1	Left Rail	
1	Right Rail	
1	Rack Base	
1	Left Support Brace	
1	Right Support Brace	
1	Top Angle	
16	1/4-20 x 0.625" screws	
16	1/4-20 keps nuts	
16	0.625in washers	
1	Assembly Instructions	

Tags: **Relay Rack, H-Frame, Server Rack, Equipment Rack, Network Rack, Skeleton Rack, Telco Rack,** *Data subject to change without notice*
Two-Post Rack, knock-down, knock down

© 2025. Hammond Manufacturing Ltd. All rights reserved.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hammond:](#)

[DNRR1970LDK](#) [DNRR1984LDK](#) [DNRR1942LDK](#) [DNRR1977LDK](#) [DNRR1963LDK](#)