



Quality Products. Service Excellence.

Vented Top Panel C2TV Series

Features



- Use with **C2, C2RR, C4, C4RR, H1, RCK** or **CLC** cabinet series.
 - H1 requires H1TC Series for mounting.
- 14 gauge steel construction.
- Provides passive airflow venting for cabinets.
 - CE versions include cable entry grommets in all four (4) corners.
- **CLPKIT832-6** Cabinet mounting hardware included.
- Finished in RAL9005 black or ASA61 gray powder paint coat. Complies with the Greenguard guidelines for indoor air quality.
- TAA-compliant for GSA Schedule purchases.
- RoHS and REACH compliant.
- Manufactured in North America.

Part No. Black	Part No. Light Gray	Overall Dimesnsions		Cable Entry
		Width	Depth	
C2T1923VBK1	C2T1923VLG1	20.00	15.00	No
C2T1931VBK1	C2T1931VLG1	20.00	23.75	No
C2T1936VBK1	C2T1936VLG1	20.00	28.25	No
C2T2431VBK1	C2T2431VLG1	25.00	23.75	No
C2T2436VBK1	C2T2436VLG1	25.00	28.25	No
C2T1923VCEBK1	C2T1923VCELG1	20.00	14.50	Yes
C2T1931VCEBK1	C2T1931VCELG1	20.00	23.25	Yes
C2T1936VCEBK1	C2T1936VCELG1	20.00	27.75	Yes

Cabinet Sizing Chart

Fan Top Size	C2 Cabinet		C4 Cabinet		DCZ4 Cabinet		H1 Cabinet	RCK Cabinet
	Width	Depth	Width	Depth	Width	Depth		
C2T1923*	23.00	23.63	24.00	31.50	-	-	All Sizes	All Sizes
C2T1931*	23.00	31.50	24.00	36.00	-	-	-	-
C2T1936*	23.00	36.00	24.00	42.00	-	-	-	-
C2T2423*	-	-	30.00	31.50	-	-	-	-
C2T2431*	-	-	30.00	36.00	30.00	42.00	-	-
C2T2436*	-	-	30.00	42.00	-	-	-	-

What's Inside the Box

Qty Included	Description	Replacement Part No.
1	Top Panel	
6	8-32 Clip Nut (Black Oxide Finish)	CLPKIT832-6
6	8-32 x 0.5" Machine Screw (Zinc Plated)	CLPKIT832-6

Data subject to change without notice

© 2024. Hammond Manufacturing Ltd. All rights reserved.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hammond:](#)

[C2T1931VBK1](#) [C2T1936VBK1](#) [C2T1923VBK1](#) [C2T1936VCEBK1](#) [C2T1931VCEBK1](#) [C2T1923VCEBK1](#)
[C2T1931VLG1](#) [C2T1923VCELG1](#) [C2T1936VCELG1](#) [C2T1923VLG1](#) [C2T1931VCELG1](#) [C2T1936VLG1](#)
[C2T2431VBK1](#) [C2T2431VLG1](#) [C2T2436VBK1](#) [C2T2436VLG1](#)