



Quality Products. Service Excellence.

Filter Fan Kits *DNFF Series*

The DNFF Fan kit is ideal when sealing a cabinet or enclosure. Unlike the **DNFK**, the DNFF does not include an AC plug as it is designed to be hard-wired with or without a thermostat.



Features

- Kit includes one (1) of the following:
 - Fan
 - Plastic Filter Grill
 - Filter
 - Metal Grill
 - Wire Cord or Leads (see table)
 - Includes Mounting Hardware
- Flame retardant, ABS plastic filter fan grill is moulded in a choice of four finishes to match our racks & accessories.
 - "BK" (Black)
 - "GY" (ANSI 61 Gray)
 - "LG" (Light Gray - RAL7035)
- Fan component is UL recognized to UL 507, and cUL recognized or CSA certified to CSA C22.2 No. 113.
- The filter is designed to meet IP5X dust resistance.
- If required, complementary exhaust filter grill kits (without fan) available - see **XPFA Series**

Accessories

- Metal Fan Guard
- Filter Fan Grills
- Thermostats
- Fan Cords

Filter Fan (Always On)

Part No. Black Filter Grill	Part No. ANSI 61 Gray Filter Grill	Part No. Light Gray Filter Grill	VAC	Fan Size	CFM	Cord Length	Noise (dB)
DNFF080BK115	DNFF080GY115	DNFF080LG115	115	3.15	32	11 Inch leads	34
DNFF120BK115	DNFF120GY115	DNFF120LG115	115	4.70	105	24 Inch cord	56
DNFF150BK115	DNFF150GY115	DNFF150LG115	115	6.00	230	12 Inch leads	53
DNFF254BK115	DNFF254GY115	DNFF254LG115	115	10.00	550	24 Inch cord	60
DNFF080BK230	DNFF080GY230	DNFF080LG230	230	3.15	32	11 Inch leads	34
DNFF120BK230	DNFF120GY230	DNFF120LG230	230	4.70	105	24 Inch cord	56
DNFF150BK230	DNFF150GY230	DNFF150LG230	230	6.00	230	12 Inch leads	53
DNFF254BK230	DNFF254GY230	DNFF254LG230	230	10.00	550	24 Inch cord	60

Replacement Filters (Sold in Pack of 5)

Part No.	Use with Fan Size	Use with XPFA Series	Use with DNFF Series
PFF1000	3.15	XPFA80	DNFF080
PFF2000	4.70	XPFA120	DNFF120
PFF4000	7.72	XPFA150	DNFF150

Part No.	Use with Fan Size	Use with XPFA Series	Use with DNFF Series
PFF6000	12.00	XPFA254	DNFF254

Data subject to change without notice

© 2025. Hammond Manufacturing Ltd. All rights reserved.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hammond:](#)

<u>DNFF080BK230</u>	<u>DNFF080LG230</u>	<u>DNFF080CG230</u>	<u>DNFF080GY230</u>	<u>DNFF120LG230</u>	<u>DNFF120BK230</u>
<u>DNFF080BK115</u>	<u>DNFF080GY115</u>	<u>DNFF120GY230</u>	<u>DNFF080LG115</u>	<u>DNFF120CG230</u>	<u>DNFF080CG115</u>
<u>DNFF120LG115</u>	<u>DNFF120GY115</u>	<u>DNFF120BK115</u>	<u>DNFF254BK115</u>	<u>DNFF150GY115</u>	<u>DNFF150GY230</u>
<u>DNFF150BK115</u>	<u>DNFF150BK230</u>	<u>DNFF150CG115</u>	<u>DNFF150CG230</u>	<u>DNFF150LG115</u>	<u>DNFF150LG230</u>
<u>DNFF254BK230</u>	<u>DNFF254CG115</u>	<u>DNFF254CG230</u>	<u>DNFF254GY115</u>	<u>DNFF254GY230</u>	<u>DNFF254LG115</u>
<u>DNFF254LG230</u>	<u>DNFF120CG115</u>				