



Quality Products. Service Excellence.

Type 4X Polyester Single/Two Door Freestanding Enclosure *PJFS*

Series

Continuous Hinge Door with Handle



Application

- Designed for use as instrument enclosures, electric, hydraulic, or pneumatic control housings, electrical junction boxes, or terminal wiring enclosures.
- Provides outstanding insulation and protection where equipment may be hosed down or be very wet.
- Ideal in applications with high temperatures or highly corrosive environments.

Standards

- UL 508A Type 1, 2, 3, 4, 4X, 12 and 13
- cUL Type 1, 2, 3, 4, 4X, 12 and 13 per CSA 22.2 No. 94
- Complies with
 - IEC 60529, IP66
 - NEMA Type 1, 2, 3, 4, 4X, 12 and 13

Construction

- Fiberglass polyester enclosure with matching door is easily punched, cut, or drilled.
- Enhanced UV inhibitors protect against outdoor weathering.
- Collar Studs are provided for optional inner panel(s).
- Two door enclosure accommodates 2 separate inner panels
- Mounting hardware included.
- Heavy duty continuous 304 SS Hinge.
- Flexible self-gripping gasket compresses over flange for tight seal.
- 3-point SS handle with pad lock provision.
- Molded-in drip shield.
- Fiberglass mounting strut side walls on double door unit.
- Operating temperatures between 130°C and -40°C (266°F to -40°F).
- Impact index of 6.78J (5 ft/lb).
- For corrosion resistance information, please refer to table in the **Technical Information** section.

Finish

- Fiberglass polyester material has a gray finish.
- Optional inner panels are available in white powder coated finished steel.

Accessories

- Window Kits
- General Accessories
- Climate Control

**New and improved PDF part
drawing files with more detail
now available.**

Click part number in table below
to access PDF, DXF, and STEP files.

Part No.	Enclosure			Optional Inner Panel		Part No.
	H	W	D	H	W	
PJFS722525	72.00	25.00	24.50	57.00	21.00	18P5721
PJFS724925DD	72.00	48.00	24.50	57.00	21.00	18P5721

DD version is a double door unit. Order 2 inner panels for double door enclosure.

Tags: **PJ, polyester, freestanding, double door, single door, fiberglass, non-metallic, NEMA 4X, Type 4X, outdoor, continuous hinge, handle** *Data subject to change without notice*

© 2024. Hammond Manufacturing Ltd. All rights reserved.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hammond:](#)

[PJFS724925DD](#) [PJFS722525](#)