



Quality Products. Service Excellence.

## 2-Post Open Frame Rack *RRTT Series*

Load rated to 350 lbs (159 kg)



### Features:

- Constructed in 14-gauge steel.
- EIA compliant 19 inch mounting rails with punched round holes for use with clip nuts.
- Includes starter pack of **CLPKIT1032-25** screws and clip nuts.
- Includes large base for freestanding support of equipment.
- Finished in textured black powder paint. Complies with the Greenguard guidelines for indoor air quality.
- Self-squaring design ships un-assembled (some assembly required).
- 350 lbs (159 kg) **static load rating**.
- TAA-compliant for GSA Schedule purchases.
  - BAA/TAA-compliant documentation available upon request.
- RoHS Compliant.
- Manufactured in North America within an ISO 9001:2015 certified facility.



### Accessories

- Cable Managers
- Hinged Clear Security Cover
- Adjustable Rack Shelf
- Deep Channel Rack Shelf
- Keyboard & Equipment Rack Shelf
- Adjustable Rack Mount DIN Rail Kit
- 10-32 Mounting Hardware
- PDUs and Outlet Strips
- Rack Panels
- Universal Rack Shelf
- Variable-Depth Rack Shelf
- Centered Rack Shelf
- Clamping Rack Shelf
- Rack Unit Label
- Bonding and Grounding



Part No.	Height	Overall Dimensions		Rack Units	Mounting Dimensions	
		Width	Base Depth		Height	Width
RRTT1921BK1	24.00	20.38	12.00	12U	21.00	19.00
RRTT1928BK1	31.00	20.38	12.00	16U	28.00	19.00

### Turn your RRTT into an Adjustable Depth 4-Post Rack

Order Two (2) of following:		Order One (1) or Two (2) of the following:		Rack	Min	Max
RRTT Rack	Adjustable Depth Rack Shelf	Adjustable Depth Angle Brackets	Units	Depth	Depth	Depth
RRTT1921BK1	ADSU1825BK	-	12U	18.00	25.00	
RRTT1921BK1	ADSU2536BK	RAAB2436BK	12U	25.00	36.00	

Order Two (2) of the following:		Order One (1) or Two (2) of the following:		Rack	Min	Max
RRTT Rack	Adjustable Depth Rack Shelf	Adjustable Depth Angle Brackets		Units	Depth	Depth
RRTT1921BK1	ADSU3642BK	RAAB3648BK		12U	36.00	42.00
RRTT1928BK1	ADSU1825BK	-		16U	18.00	25.00
RRTT1928BK1	ADSU2536BK	RAAB2436BK		16U	25.00	36.00
RRTT1928BK1	ADSU3642BK	RAAB3648BK		16U	36.00	42.00

Tags: Relay Rack, H-Frame, Homelab, Server Rack, Equipment Rack, Network Rack, Skeleton Rack, Telco Rack, Two-Post Rack, knock-down, knock down *Data subject to change without notice*

© 2025. Hammond Manufacturing Ltd. All rights reserved.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hammond:](#)

[RRTT1928BK1](#) [RRTT1921BK1](#)