




*Quality Products. Service Excellence.*

## Vertical Cable Tray VCT Series



### Features

- Constructed in 16-gauge steel.
- Designed to fit most Hammond cabinets and may be compatible with cabinets made by others.
- The folded (flange) edges increase strength and ease of managing cables.
- The VCT and VCTPDU Series includes cutouts for installing cable ties or hook and loop tie-offs.
- The VCTPDU also includes cutouts for toolless mounting of most PDUs that include a round plastic shouldered button.
- Includes mounting hardware.
- Finished in textured RAL9005 black powder paint finish.
- TAA-compliant for GSA Schedule purchases.
- RoHS and REACH compliant.
- Manufactured in North America.

### Accessories

- Hook and Loop Convenience Roll
- Cabinet Rail Mounting Hardware



| Part No. | Overall Dimensions |       |       | Mounting Dimensions |            | Includes Toolless<br>PDU Mounting | Product<br>Compatibility      |
|----------|--------------------|-------|-------|---------------------|------------|-----------------------------------|-------------------------------|
|          | Height             | Width | Depth | Height              | Rack Units |                                   |                               |
| VCT28    | 28.00              | 3.00  | 0.50  | 28.00               | 16U        | No                                | RCHS, RCHV                    |
| VCT42    | 42.00              | 3.00  | 0.50  | 42.00               | 24U        | No                                | C2, C4, HWM, REFK             |
| VCT49    | 49.00              | 3.00  | 0.50  | 49.00               | 28U        | No                                | C2, REFK                      |
| VCT56    | 56.00              | 3.00  | 0.50  | 56.00               | 32U        | No                                | C2, HWM, REFK                 |
| VCT63    | 63.00              | 3.00  | 0.50  | 63.00               | 36U        | No                                | C2, REFK                      |
| VCT70    | 70.00              | 3.00  | 0.50  | 70.00               | 40U        | No                                | C2, REFK                      |
| VCT73    | 73.00              | 3.00  | 0.50  | 73.00               | 42U        | No                                | C2, C4, CLC, H1, REFK, HDME20 |
| VCT77    | 77.00              | 3.00  | 0.50  | 77.00               | 44U        | No                                | C2, C4, REFK                  |
| VCT78    | 78.75              | 3.00  | 0.50  | 78.75               | 45U        | No                                | C2, C4, REFK, HDME20          |
| VCT85    | 85.00              | 3.00  | 0.50  | 85.00               | 48U        | No                                | C2, REFK                      |
| VCTPDU73 | 73.50              | 6.00  | 0.50  | 73.50               | 42U        | Yes                               | C2, C4, CLC, H1, REFK, HDME20 |
| VCTPDU77 | 77.00              | 6.00  | 0.50  | 77.00               | 44U        | Yes                               | C2, C4, CLC, REFK             |

| Overall Dimensions |        |       | Mounting Dimensions |        | Includes Tooless |              | Product                   |
|--------------------|--------|-------|---------------------|--------|------------------|--------------|---------------------------|
| Part No.           | Height | Width | Depth               | Height | Rack Units       | PDU Mounting | Compatability             |
| VCTPDU78           | 78.75  | 6.00  | 0.50                | 78.75  | 45U              | Yes          | C2, C4, CLC, REFK, HDME20 |

Data subject to change without notice

© 2025. Hammond Manufacturing Ltd. All rights reserved.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hammond:](#)

[VCT70](#) [VCT77](#) [VCT73](#) [VCTPDU73](#) [VCTPDU78](#) [VCTPDU77](#) [VCT78](#) [VCT42](#) [VCT49](#) [VCT56](#) [VCT63](#) [VCT85](#)