




1	2	3	4	5	6	7	8
---	---	---	---	---	---	---	---


7	8
---	---




X
male



Loading-Plan:



Y
male



- Temperature range: -40°C ... +70°C

		All Dimensions in mm		Tech. Character.		Free size tol.		According to production drawing	
		All rights reserved		Created by STOCHECIC		Inspected by COSTEA		Standardisation MUNTEANV	
Department HCS - RO		Date 2018-04-19		State Final Release		Title Han 3A RJ45 Cable Assembly		Doc-Key / ECM-Nr. 100081046/UGD/010/D 500000133904	
HARTING Customised Solutions D-32339 Espelkamp		Type TB		Number 0945715XXXX		Rev. D		Page 1/2	

1				2				3				4				5				6				7				8			
A	51	09457151126	RJ45 Ethernet standard cable, AWG22/1, 2x2x0.64, PVC, Cat. 5+, green	4	95	09457151183	RJ45 Ethernet stranded cable, 4xAWG22/7, PVC, Cat. 5+, green	100																							
	50	09457151125		3	94	09457151182		90																							
	49	09457151124		2	93	09457151181		80																							
	48	09457151123		1.5	92	09457151180		70																							
	47	09457151122		1	91	09457151179		60																							
B	46	09457151121	RJ45 Ethernet stranded cable, AWG22/7, 2x2x0.75, outdoor, PVC, Cat. 5+, black	0.5	90	09457151178	50																								
	45	09457150083		100	89	09457151177	40																								
	44	09457150082		90	88	09457151176	30																								
	43	09457150081		80	87	09457151175	20																								
	42	09457150080		70	86	09457151174	15																								
C	41	09457150079	RJ45 Ethernet trailing cable, AWG22/7, 2x2x0.75, PUR, Cat. 5+, green	60	85	09457151173	10																								
	40	09457150078		50	84	09457151172	9																								
	39	09457150077		40	83	09457151171	8																								
	38	09457150076		30	82	09457151185	7.5																								
	37	09457150075		20	81	09457151170	7																								
D	36	09457150074	RJ45 Ethernet standard cable, AWG22/1, 2x2x0.64, PVC, Cat. 5+, green	15	80	09457151169	6																								
	35	09457150073		10	79	09457151168	5																								
	34	09457150072		9	78	09457151167	4																								
	33	09457150071		8	77	09457151166	3																								
	32	09457150070		7	76	09457151165	2																								
E	31	09457150069	RJ45 Ethernet standard cable, AWG22/1, 2x2x0.64, PVC, Cat. 5+, green	6	75	09457151164	1.5																								
	30	09457150068		5	74	09457151163	1																								
	29	09457150067		4	73	09457151162	0.5																								
	28	09457150066		3	72	09457151161	100																								
	27	09457150065		2	71	09457151160	90																								
F	26	09457150064	RJ45 Ethernet standard cable, AWG22/1, 2x2x0.64, PVC, Cat. 5+, green	1.5	70	09457151144	85																								
	25	09457150063		1	69	09457151159	80																								
	24	09457150062		0.5	68	09457151158	70																								
	23	09457150061		100	67	09457151143	65																								
	22	09457150060		90	66	09457151157	60																								
G	21	09457150059	RJ45 Ethernet standard cable, AWG22/1, 2x2x0.64, PVC, Cat. 5+, green	80	65	09457151142	55																								
	20	09457150058		70	64	09457151156	50																								
	19	09457150057		60	63	09457151155	40																								
	18	09457150056		50	62	09457151141	35																								
	17	09457150055		40	61	09457151154	30																								
H	16	09457150054	RJ45 Ethernet standard cable, AWG22/1, 2x2x0.64, PVC, Cat. 5+, green	30	60	09457151140	25																								
	15	09457150090		25	59	09457151153	20																								
	14	09457150053		20	58	09457151152	15																								
	13	09457150052		15	57	09457151151	10																								
	12	09457150051		10	56	09457151131	9																								
I	11	09457150031	RJ45 Ethernet standard cable, AWG22/1, 2x2x0.64, PVC, Cat. 5+, green	9	55	09457151130	8																								
	10	09457150030		8	54	09457151129	7																								
	9	09457150029		7	53	09457151128	6																								
	8	09457150028		6	52	09457151127	5																								
	7	09457150027		5	Cont. no.	Part no.	Type of cable	Dim. a[m]																							
J	6	09457150026	RJ45 Ethernet standard cable, AWG22/1, 2x2x0.64, PVC, Cat. 5+, green	4	RJ45 Ethernet standard cable, AWG22/1, 2x2x0.64, PVC, Cat. 5+, green			100																							
	5	09457150025		3																											
	4	09457150024		2																											
	3	09457150023		1.5																											
	2	09457150022		1																											
K	1	09457150021	RJ45 Ethernet standard cable, AWG22/1, 2x2x0.64, PVC, Cat. 5+, green	0.5	RJ45 Ethernet standard cable, AWG22/1, 2x2x0.64, PVC, Cat. 5+, green			100																							
	Cont. no.	Part no.		Type of cable					Dim. a[m]																						

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09457150023](#) [09457150027](#) [09457150051](#) [09457150053](#) [09457151123](#) [09457151125](#) [09457151151](#)
[09457151153](#) [09457151156](#) [09457151161](#) [09457151166](#) [09457151173](#) [09457151175](#) [09457151178](#) [09457151127](#)
[09457151152](#) [09457151154](#) [09457151177](#) [09457151164](#) [09457151168](#) [09457151165](#) [09457150066](#)
[09457151183](#) [09457150064](#)