










Side entry hoods with knurled screws

Identification	No. of contacts	Part number	Drawing	Dimensions in mm																																			
Hood¹⁾ grey thermoplastic RAL 7032	9 15 25 37 50	09 67 009 0571 09 67 015 0571 09 67 025 0571 09 67 037 0571 09 67 050 0571	Upper hood part 9 contacts  15 – 50 contacts  <table><tr><th></th><th>a max.</th><th>b min.</th><th>c</th><th>d</th><th>e</th><th>f</th></tr><tr><td>15</td><td>39.62</td><td>28.40</td><td>13.00</td><td>14.00</td><td>1.00</td><td>7.50</td></tr><tr><td>25</td><td>53.52</td><td>42.20</td><td>13.00</td><td>14.00</td><td>1.00</td><td>7.50</td></tr><tr><td>37</td><td>69.80</td><td>58.65</td><td>13.00</td><td>14.00</td><td>1.00</td><td>7.50</td></tr><tr><td>50</td><td>67.41</td><td>56.18</td><td>16.00</td><td>17.50</td><td>1.50</td><td>9.50</td></tr></table>		a max.	b min.	c	d	e	f	15	39.62	28.40	13.00	14.00	1.00	7.50	25	53.52	42.20	13.00	14.00	1.00	7.50	37	69.80	58.65	13.00	14.00	1.00	7.50	50	67.41	56.18	16.00	17.50	1.50	9.50	Lower hood part  
	a max.	b min.	c	d	e	f																																	
15	39.62	28.40	13.00	14.00	1.00	7.50																																	
25	53.52	42.20	13.00	14.00	1.00	7.50																																	
37	69.80	58.65	13.00	14.00	1.00	7.50																																	
50	67.41	56.18	16.00	17.50	1.50	9.50																																	
grey thermoplastic with internal tin-plate screening	9 15 25 37 50	09 67 009 0573 09 67 015 0573 09 67 025 0573 09 67 037 0573 09 67 050 0573																																					
9-37 way for packaging density of 3 TE (15.24 mm)																																							
Knurled screw Thread UNC Thread M3	9-50	09 67 000 9971²⁾ 09 67 001 9965*	 Grey head / Nickel plated steel  Full metal part																																				
Tooling for assembly of hoods Top part Bottom part		09 99 000 0215* 09 99 000 0216*																																					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HARTING:

[09990000216](#) [09990000215](#) [09185647913800](#)