

Han3A RJ45 10G Cat6 PFT 8p with cover



Image is for illustration purposes only. Please refer to product description.

| | |
|--------------------|---|
| Part number | 09 45 215 1562 |
| Specification | Han3A RJ45 10G Cat6 PFT 8p with cover |
| HARTING eCatalogue | https://b2b.harting.com/09452151562 |

Identification

| | |
|---------------|-----------------------------------|
| Category | Connectors |
| Series | RJ45 |
| Element | Panel feed through |
| Specification | Straight, with self-closing cover |

Version

| | |
|--------------------|--|
| Size | Han [®] 3 A |
| Shielding | Fully shielded, 360° shielding contact |
| Number of contacts | 8 |
| Fixing | Screwable in cover plates |

Technical characteristics

| | |
|--|--|
| Limiting temperature | -40 ... +70 °C |
| Mating cycles | ≥500 |
| Degree of protection acc. to IEC 60529 | IP65 IP67 |
| Transmission characteristics | Cat. 6 Class E up to 250 MHz |
| Data rate | 10 Mbit/s 100 Mbit/s 1 Gbit/s 10 Gbit/s |

Material properties

| | |
|-------------------------|---------------|
| Material (hood/housing) | Zinc die-cast |
|-------------------------|---------------|



Pushing Performance

Material properties

| | |
|-----------------------------|---|
| Surface (hood/housing) | Powder-coated |
| Colour (hood/housing) | Grey |
| RoHS | compliant with exemption |
| RoHS exemptions | 6(a) / 6(a)-I: Lead as an alloying element in steel for machining purposes and in galvanised steel containing up to 0,35 % lead by weight / Lead as an alloying element in steel for machining purposes containing up to 0,35 % lead by weight and in batch hot dip galvanised steel components containing up to 0,2 % lead by weight |
| ELV status | compliant with exemption |
| China RoHS | 50 |
| REACH Annex XVII substances | No |
| REACH ANNEX XIV substances | No |
| REACH SVHC substances | Yes |
| REACH SVHC substances | Lead |

Specifications and approvals

| | |
|-----------|--|
| Approvals | DNV GL |
| UL / CSA | UL 1977 ECBT2.E102079 CSA-C22.2 No. 182.3 ECBT8.E102079 |
| PROFINET | Yes |

Commercial data

| | |
|--------------------------------|---------------------------------------|
| Packaging size | 1 |
| Net weight | 87 g |
| Country of origin | Romania |
| European customs tariff number | 85366990 |
| eCl@ss | 27440101 Rectangular connectors (set) |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09452151562](#)