

## PP-V4-CA-USB3A-PP/IP20-P-P-STR-5.0




Image is for illustration purposes only. Please refer to product description.

Part number	09 45 445 2915
Specification	PP-V4-CA-USB3A-PP/IP20-P-P-STR-5.0
HARTING eCatalogue	<a href="https://b2b.harting.com/09454452915">https://b2b.harting.com/09454452915</a>

### Identification

Category	Cable assemblies
Series	USB
Specification	Pre-assembled on both sides
Connector 1	HARTING PushPull (V4) USB 3.0 Type A
Connector 2	IP20 USB 3.0 Type A
Type of cable	Copper cable (round)

### Version

Cable length	5 m
Number of cores	8
Core structure	4x AWG 26/7 2x AWG 28/7 2x AWG 22/7

### Technical characteristics

Rated current	1.5 A
Rated voltage	30 V DC
Insulation resistance	$>10^8 \Omega$
Contact resistance	$\leq 30 \text{ m}\Omega$
Limiting temperature	-40 ... +85 °C
Insertion force	$\leq 35 \text{ N}$
Withdrawal force	$\geq 15 \text{ N}$



Pushing Performance

## Technical characteristics

Mating cycles	≥750
Degree of protection acc. to IEC 60529	IP65 IP67
Cable diameter	6.2 mm
Test voltage $U_{r.m.s.}$	0.5 kV (contact-contact) 0.5 kV (contact-ground)
Data rate	5 Gbit/s
Impedance	90 $\Omega \pm 15 \%$

## Material properties

Material (insert)	Liquid crystal polymer (LCP)
Material (contacts)	Copper alloy
Surface (contacts)	Sn over Ni Termination side Au over Ni Mating side
Material (cable)	PVC
Colour (cable)	Black
Material (overmoulding)	Polyamide (PA)
Colour (overmoulding)	Black
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

## Specifications and approvals

Specifications	IEC 61076-3-106 Variant 4 (V4)
----------------	--------------------------------

## Commercial data

Packaging size	1
Net weight	284 g
Country of origin	Malaysia
European customs tariff number	85444290



Pushing Performance

## Commercial data

eCl@ss

27060390 Ready-made data cable (unspecified)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HARTING:

09454452915