

Han 1A-2+PE-s-f



Image is for illustration purposes only. Please refer to product description.

Part number	09 10 002 2705
Specification	Han 1A-2+PE-s-f
HARTING eCatalogue	https://b2b.harting.com/09100022705

Identification

Category	Inserts
Series	Han® 1A

Version

Termination method	Screw termination
Gender	Female
Locking type	Single locking lever
Size	1 A
Number of contacts	2
PE contact	Yes
Details	Order separately the single wire seal or the hoods/housings for an IP65 performance. Please order locking lever separately.

Details

A Han® 1A configuration that only consists of inserts (with or without strain relief, 09 10 000 5300) is an unenclosed connector acc. to IEC 61984. In this case protection against electric shock must be provided by the installation methods of the user.

Technical characteristics

Conductor cross-section	0.75 ... 1.5 mm ²
Rated current	10 A
Rated voltage conductor-earth	230 V
Rated voltage conductor-conductor	400 V
Rated impulse voltage	4 kV
Pollution degree	3



Pushing Performance

Technical characteristics

Insulation resistance	$>10^8 \Omega$
Limiting temperature	-30 ... +90 °C
Tightening torque	0.25 Nm
Mating cycles	≥ 100
Degree of protection acc. to IEC 60529	IP20

Material properties

Material (insert)	Polyamide (PA)
Colour (insert)	RAL 9005 (jet black)
Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
Material (seal)	NBR
Colour (seal)	Black
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

Specifications and approvals

Specifications	EN 45545-2 R22: HL1, HL2, HL3
	EN 45545-2 R23: HL1, HL2, HL3
	EN 45545-2 R24: HL1, HL2, HL3
	IEC 61373 Category 1 Class B
	EN 60664-1
	IEC 61984
Approvals	DNV GL

Commercial data

Packaging size	1
Net weight	13.3 g
Country of origin	Germany



Pushing Performance

Commercial data

European customs tariff number 85366990

eCl@ss 27440205 Contact insert for industrial connectors

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HARTING:

09100022705