

PFT M12 crimp shielded D-cod. 4pol. male



Image is for illustration purposes only. Please refer to product description.

Part number	21 03 882 1425
Specification	PFT M12 crimp shielded D-cod. 4pol. male
HARTING eCatalogue	https://b2b.harting.com/21038821425

Identification

Category	Connectors
Series	Circular connectors M12
Element	Cable connector Panel feed through
Specification	for rear mounting

Version

Termination method	Crimp termination
Gender	Male
Locking type	Screw locking
Shielding	Shielded
Number of contacts	4
Coding	D-coding
Details	Please order crimp contacts separately.
Details	For Fast Ethernet applications only

Technical characteristics

Conductor cross-section	0.14 ... 0.75 mm ²
Conductor cross-section	AWG 26 ... AWG 18
Wire outer diameter	≤2.3 mm
Rated current	4 A
Rated voltage	250 V
Rated impulse voltage	1.5 kV



Pushing Performance

Technical characteristics

Pollution degree	3
Insulation resistance	$>10^8 \Omega$
Contact resistance	$\leq 10 \text{ m}\Omega$
Tightening torque	2 Nm Lock nut
Ambient temperature	-40 ... +85 °C
Mating cycles	≥ 500
Degree of protection acc. to IEC 60529	IP65 / IP67 when mated
Cable diameter	4.5 ... 8.8 mm
Transmission characteristics	Cat. 5 Class D up to 100 MHz
Overvoltage category	III
Isolation group	I ($600 \leq \text{CTI}$)
Thickness of the panel	2.5 ... 4.5 mm

Material properties

Material (insert)	Polyamide (PA)
Material (hood/housing)	Zinc die-cast
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

Specifications and approvals

Specifications	IEC 61076-2-101
UL / CSA	UL 1977 ECBT2.E102079 CSA-C22.2 No. 182.3 ECBT8.E102079
PROFINET	Yes

Commercial data

Packaging size	10
Net weight	44 g



Pushing Performance

Commercial data

Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440102 Circular connector (for field assembly)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HARTING:

21038821425