







X

Loading-Plan:



- Protection level: IP20
- Temperature range: -40°C ... +70°C

		All Dimensions in mm Original Size DIN A3		Scale 2:1		Free size tol.		Ref.							
								Sub.							
		All rights reserved		Created by MUNTEANV		Inspected by AVRAM		Standardisation HOFFMANN		Date 2016-01-25		State Final Release			
		Department EC PD - RO		Title RJ Industrial Cable Assembly								Doc-Key / ECM-Nr. 100177621/UGD/010/D 50000099449			
HARTING Electronics GmbH D-32339 Espelkamp				Type TB		Number 09470600XXX						Rev. D		Page 1/2	

1		2		3		4		5		6		7		8	
A	52	09470600052		RJ45 Ethernet trailing cable, AWG22/7, 2x2x0.75, PUR, Cat. 5+, green		6.5±0.2	6								A
	51	09470600051					5								
	50	09470600050					4								
	49	09470600049					3								
	48	09470600048					2								
	47	09470600047		1.5								B			
	46	09470600046		1											
	45	09470600045		0.5											
	44	09470600044		100											
	43	09470600043		90											
B	42	09470600042		80											
	41	09470600041		70											
	40	09470600040		60											
	39	09470600039		50											
	38	09470600038		40											
	37	09470600037		30											
	36	09470600036		20											
	35	09470600035		15											
	34	09470600034		10											
	33	09470600033		9											
C	32	09470600032		8											
	31	09470600031		7											
	30	09470600030		6											
	29	09470600029		5											
	28	09470600028		4											
	27	09470600027		3											
	26	09470600026		2											
	25	09470600025		1.5											
	24	09470600024		1											
	23	09470600023		0.5											
D	22	09470600022		100											
	21	09470600021		90											
	20	09470600020		80											
	19	09470600019		70											
	18	09470600018		60											
	17	09470600017		50											
	16	09470600016		40											
	15	09470600015		30											
	14	09470600014		20											
	13	09470600013		15											
E	12	09470600012		10											
	11	09470600011		9											
	10	09470600010		8											
	9	09470600009		7											
	8	09470600008		6											
	7	09470600007		5											
	6	09470600006		4											
	5	09470600005		3											
	4	09470600004		2											
	3	09470600003		1.5											
F	2	09470600002		1											
	1	09470600001		0.5											
	Cont. no.	Part no.	Type of cable	Dim. d [mm]									Dim. a [m]		

90	09470600090	RJ45 Ha-VIS EtherRail, Flexible data cable, AWG22/7, 4x0.25, Cat. 5/5e, black		6.6±0.2	0.5
89	09470600088	RJ45 Ethernet stranded cable, AWG22/7, 2x2x0.75, outdoor, PVC, Cat. 5+, black		6.5±0.2	100
88	09470600087				90
87	09470600086				80
86	09470600085				70
85	09470600084				60
84	09470600083				50
83	09470600082				40
82	09470600081				30
81	09470600080				20
80	09470600079				15
79	09470600089				13
78	09470600078				10
77	09470600077				9
76	09470600076				8
75	09470600075				7
74	09470600074				6
73	09470600073				5
72	09470600072				4
71	09470600071				3
70	09470600070				2
69	09470600069	1.5			
68	09470600068	1			
67	09470600067	0.5			
66	09470600066	RJ45 Ethernet trailing cable, AWG22/7, 2x2x0.75, PUR, Cat. 5+, green			100
65	09470600065				90
64	09470600064				80
63	09470600063				70
62	09470600062				60
61	09470600061				50
60	09470600060				40
59	09470600059				30
58	09470600058				20
57	09470600057				15
56	09470600056	10			
55	09470600055	9			
54	09470600054	8			
53	09470600053	7			
Cont. no.	Part no.	Type of cable		Dim. d [mm]	Dim. a [m]

	All rights reserved Department EC PD - RO	Scale 1:1	Free size tol.		Ref.	
				Sub.		
	HARTING Electronics GmbH D-32339 Espelkamp	Created by MUNTEANV	Inspected by AVRAM	Standardisation HOFFMANN	Date 2016-01-25	State Final Release
		Title RJ Industrial Cable Assembly				Doc-Key / ECM-Nr. 100177621/UGD/010/D 500000099449
		Type TB	Number 09470600XXX			Rev. D
					Page 2/2	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HARTING:

[09470600002](#) [09470600023](#) [09470600024](#) [09470600025](#) [09470600026](#) [09470600027](#) [09470600029](#)
[09470600045](#) [09470600046](#) [09470600048](#) [09470600049](#) [09470600051](#) [09470600031](#) [09470600047](#) [09470600001](#)
[09470600007](#)