

Han Q 8/0-HBM Metal



Image is for illustration purposes only. Please refer to product description.

| | |
|--------------------|---|
| Part number | 09 12 008 0301 |
| Specification | Han Q 8/0-HBM Metal |
| HARTING eCatalogue | https://harting.com/09120080301 |

Identification

| | |
|--------------------------|--------------------------|
| Category | Hoods / Housings |
| Series of hoods/housings | Han-Compact® |
| Type of hood/housing | Bulkhead mounted housing |

Version

| | |
|----------------------|--|
| Size | Han-Compact® |
| Locking type | Single locking lever |
| Field of application | Hoods/housings for industrial applications |

Technical characteristics

| | |
|--|--|
| Limiting temperature | -40 ... +125 °C |
| Note on the limiting temperature | For use as a connector according to IEC 61984. |
| Degree of protection acc. to IEC 60529 | IP65 |
| Type rating acc. to UL 50 / UL 50E | 12 |

Material properties

| | |
|-------------------------|----------------------|
| Material (hood/housing) | Zinc die-cast |
| Surface (hood/housing) | Chromated |
| Colour (hood/housing) | RAL 9005 (jet black) |
| Material (seal) | NBR |
| Material (locking) | Stainless steel |
| RoHS | not compliant |
| ELV status | not compliant |



Pushing Performance
Since 1945

Material properties

| | |
|--------------------------------------|---------------|
| China RoHS | e |
| REACH Annex XVII substances | Not contained |
| REACH ANNEX XIV substances | Not contained |
| REACH SVHC substances | Not contained |
| California Proposition 65 substances | Yes |
| California Proposition 65 substances | Lead |
| | Nickel |
| | Naphthalene |

Specifications and approvals

| | |
|-----------|-----------------------------------|
| UL / CSA | UL 1977 ECBT2.E235076 |
| | UL 2237 PVVA2.E318390 |
| | CSA-C22.2 No. 182.3 ECBT8.E235076 |
| | CSA-C22.2 No. 182.3 PVVA8.E318390 |
| Approvals | CE |
| | DNV GL |

Commercial data

| | |
|--------------------------------|--|
| Packaging size | 10 |
| Net weight | 59.5 g |
| Country of origin | Romania |
| European customs tariff number | 85389099 |
| GTIN | 5713140017542 |
| ETIM | EC000437 |
| eCl@ss | 27440202 Shell for industrial connectors |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09120080301](#)