



Pushing Performance
Since 1945

Han 24B-asg2-K-21 (AK in AI)



| | |
|--------------------|---|
| Part number | 09 30 024 2260 |
| Specification | Han 24B-asg2-K-21 (AK in AI) |
| HARTING eCatalogue | https://b2b.harting.com/09300242260 |

Identification

| | |
|-----------------------------|-------------------------|
| Category | Hoods/Housings |
| Series of hoods/housings | Han [®] B |
| Type of hood/housing | Surface mounted housing |
| Description of hood/housing | With metal cover |
| Type | Low construction |

Version

| | |
|----------------------|---|
| Size | 24 B |
| Version | Side entry |
| Cable entry | 2x Pg 21 |
| Locking type | Double locking lever (on the hood) |
| Field of application | Standard hoods/housings for industrial connectors |

Technical characteristics

| | |
|--|--|
| Limiting temperature | -40 ... +125 °C |
| Note on the limiting temperature | For use as a connector according to IEC 61984. |
| Degree of protection acc. to IEC 60529 | IP65 |
| Type rating acc. to UL 50 / UL 50E | 4 |
| | 4X |
| | 12 |

Material properties

| | |
|-------------------------|----------------------|
| Material (hood/housing) | Aluminium die-cast |
| Surface (hood/housing) | Powder-coated |
| Colour (hood/housing) | RAL 7037 (dust grey) |



Pushing Performance
Since 1945

Material properties

| | |
|--------------------------------------|----------------------------|
| Material (seal) | NBR |
| RoHS | compliant |
| ELV status | compliant |
| China RoHS | e |
| REACH Annex XVII substances | Not contained |
| REACH ANNEX XIV substances | Not contained |
| REACH SVHC substances | Not contained |
| California Proposition 65 substances | Yes |
| California Proposition 65 substances | Nickel Naphthalene |
| Fire protection on railway vehicles | EN 45545-2 (2020-08) |
| Requirement set with Hazard Levels | R1 (HL 1-3) R7 (HL 1-3) |

Specifications and approvals

| | |
|-----------|--------------|
| Approvals | CE DNV GL |
|-----------|--------------|

Commercial data

| | |
|--------------------------------|--|
| Packaging size | 1 |
| Net weight | 357.5 g |
| Country of origin | Germany |
| European customs tariff number | 85389099 |
| GTIN | 5713140047822 |
| ETIM | EC000437 |
| eCl@ss | 27440202 Shell for industrial connectors |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09300242260](#)