

# Han K 32-55-M-C




Image is for illustration purposes only. Please refer to product description.

Part number	09 38 087 3001
Specification	Han K 32-55-M-C
HARTING eCatalogue	<a href="https://b2b.harting.com/09380873001">https://b2b.harting.com/09380873001</a>

## Identification

Category	Inserts
Series	Han-Com®
Identification	Han® K 32/55

## Version

Termination method	Crimp termination
Gender	Male
Size	10 B
Number of contacts	87
Number of signal contacts	55
Number of power contacts	32
PE contact	Yes
Details	Please order crimp contacts separately.
	32x Han D®
	55x D-Sub

## Technical characteristics

Conductor cross-section	0.14 ... 2.5 mm² Power
	0.09 ... 0.52 mm² Signal
Rated current (signal)	4 A
Rated voltage (signal)	50 V
Rated impulse voltage (signal)	0.8 kV
Pollution degree (signal)	2
Rated current (power)	10 A



**Pushing Performance**  
Since 1945

## Technical characteristics

Rated voltage (power)	250 V
Rated impulse voltage (power)	4 kV
Pollution degree (power)	2
Rated voltage acc. to UL	600 V Power contacts 30 V Signal contacts
Insulation resistance	$>10^{10} \Omega$
Limiting temperature	-40 ... +125 °C
Mating cycles	$\geq 500$

## Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

## Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076

## Commercial data

Packaging size	1
Net weight	42 g
Country of origin	China
European customs tariff number	85366990



**Pushing Performance**  
Since 1945

Commercial data

GTIN	5713140186491
ETIM	EC000438
eCl@ss	27440205 Contact insert for industrial connectors

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09380873001](#)