

## RJ45 Ca. AWG 26/7, stra. PUR, IP20; 0,5m, CAT6




Image is for illustration purposes only. Please refer to product description.

|                    |   |
|--------------------|---|
| Part number        | 09 45 751 1561  |
| Specification      | RJ45 Ca. AWG<br>26/7, stra. PUR, IP20; 0,5m, CAT6                                     |
| HARTING eCatalogue | <a href="https://b2b.harting.com/09457511561">https://b2b.harting.com/09457511561</a> |

### Identification

|               |                             |
|---------------|-----------------------------|
| Category      | System cabling              |
| Series        | RJ45                        |
| Element       | Cable assemblies            |
| Specification | Pre-assembled on both sides |
| Connector 1   | HARTING RJ Industrial®      |
| Connector 2   | HARTING RJ Industrial®      |
| Type of cable | Copper cable (round)        |

### Version

|                 |                |
|-----------------|----------------|
| Cable length    | 0.5 m          |
| Number of cores | 8              |
| Core structure  | 4x 2x AWG 26/7 |

### Technical characteristics

|                              |  |
|------------------------------|--|
| Transmission characteristics | Cat. 6A Class E <sub>A</sub> up to 500 MHz |
| Data rate                    | 10 Mbit/s                                  |
|                              | 100 Mbit/s                                 |
|                              | 1 Gbit/s                                   |
|                              | 2.5 Gbit/s                                 |
|                              | 5 Gbit/s                                   |
|                              | 10 Gbit/s                                  |

### Material properties

|                  |                    |
|------------------|--------------------|
| Material (cable) | PUR (polyurethane) |
|------------------|--------------------|



**Pushing Performance**  
Since 1945

## Material properties

|                                      |               |
|--------------------------------------|---------------|
| Colour (cable)                       | Yellow        |
| RoHS                                 | compliant     |
| ELV status                           | compliant     |
| China RoHS                           | e             |
| REACH Annex XVII substances          | Not contained |
| REACH ANNEX XIV substances           | Not contained |
| REACH SVHC substances                | Not contained |
| California Proposition 65 substances | Not contained |

## Commercial data

|                                |   |
|--------------------------------|---|
| Packaging size                 | 1                                       |
| Net weight                     | 64 g                                    |
| Country of origin              | Romania                                 |
| European customs tariff number | 85444290                                |
| GTIN                           | 5713140255371                           |
| eCl@ss                         | 27060308 Patch cord copper (data cable) |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09457511561](#)