



Pushing Performance  
Since 1945

# Han® S-HBM w. MC M8-red



Image is for illustration purposes only. Please refer to product description.

Part number	09 93 001 0302
Specification	Han® S-HBM w. MC M8-red
HARTING eCatalogue	<a href="https://b2b.harting.com/09930010302">https://b2b.harting.com/09930010302</a>

## Identification

Category	Hoods/Housings
Series	Han® S
Identification	Han® S 200
Type of hood/housing	Bulkhead mounted housing
Description of hood/housing	incl. male contact with M8 bolt termination

## Version

Number of contacts	1
Locking type	Single locking lever
Field of application	Energy Storage Systems

## Technical characteristics

Rated current	200 A
Rated voltage	1,500 V
Rated impulse voltage	8 kV
Pollution degree	2
Insulation resistance	$>10^8 \Omega$
Contact resistance	$\leq 0.3 \text{ m}\Omega$
Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Number of relockings	$\geq 500$



**Pushing Performance**  
Since 1945

## Technical characteristics

Degree of protection acc. to IEC 60529	IP40 mated condition
	IP20 unmated condition (1500 V DC; 1000 V AC)

## Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
Material (hood/housing)	Polyamide (PA)
Colour (hood/housing)	RAL 3001 (signal red)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

## Specifications and approvals

Specifications	IEC 60664-1
	EN 45545-2 Fire protection on railway vehicles
	IEC 61984
	UL 1973
	UL 4128
	UL 9540
	UL 1977
Approvals	CE

## Commercial data

Packaging size	1
Net weight	34 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140183797
ETIM	EC000437



**Pushing Performance**  
Since 1945

## Commercial data

eCl@ss

27440202 Shell for industrial connectors

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09930010302](#)