




HARTING RJ Industrial RJ45, Cat. 5,
4-pole, angled overmolded, 180° position



Mating face RJ45 acc. to IEC 60603-7




Loading-Plan:



- Protection level: IP20
- Temperature range: -40°C ... +70°C

		All Dimensions in mm Original Size DIN A3		Scale 2:1		Free size tol.		Ref.					
								Sub.					
		All rights reserved		Created by MUNTEANV		Inspected by AVRAM		Standardisation HOFFMANN		Date 2016-01-25		State Final Release	
		Department EC PD - RO											
HARTING Electronics GmbH D-32339 Espelkamp		Title RJ Industrial Cable Assembly										Doc-Key / ECM-Nr. 100081066/UGD/014/D 50000099449	
		Type TB		Number 094705000XX								Rev. D	

1		2		3		4		5		6		7		8			
A	52	09470500052		RJ45 Ethernet trailing cable, AWG22/7, 2x2x0.75, PUR, Cat. 5+, green		6.5±0.2	6	RJ45 Ha-VIS EtherRail flexible data cable, AWG 22/7, 4x0.25, Cat. 5/5e, black							6.6±0.2	1.5	
	51	09470500051					5										
	50	09470500050					4										
	49	09470500049					3										
	48	09470500048					2										
	47	09470500047					1.5										
B	46	09470500046		1	RJ45 Ethernet stranded cable, 4xAWG22/7, PVC, Cat. 5+, green	6.5±0.2	100	RJ45 Ethernet stranded cable, AWG22/7, 2x2x0.75, outdoor, PVC, Cat. 5+, black							6.5±0.2	100	
	45	09470500045		90			90										
	44	09470500044		80			80										
	43	09470500043		70			70										
	42	09470500042		60			60										
	41	09470500041		50			50										
C	40	09470500040		40	RJ45 Ethernet standard cable, AWG22/1, 2x2x0.64, PVC, Cat. 5+, green	6.5±0.2	30	RJ45 Ethernet trailing cable, AWG22/7, 2x2x0.75, PUR, Cat. 5+, green							6.5±0.2	40	
	39	09470500039		20			30										
	38	09470500038		15			20										
	37	09470500037		10			15										
	36	09470500036		9			10										
	35	09470500035		8			9										
D	34	09470500034		7	RJ45 Ethernet standard cable, AWG22/1, 2x2x0.64, PVC, Cat. 5+, green	6.5±0.2	6	RJ45 Ethernet trailing cable, AWG22/7, 2x2x0.75, PUR, Cat. 5+, green							6.5±0.2	8	
	33	09470500033		6			6										
	32	09470500032		5			5										
	31	09470500031		4			4										
	30	09470500030		3			3										
	29	09470500029		2			2										
E	28	09470500028		1.5	RJ45 Ethernet standard cable, AWG22/1, 2x2x0.64, PVC, Cat. 5+, green	6.5±0.2	1	RJ45 Ethernet trailing cable, AWG22/7, 2x2x0.75, PUR, Cat. 5+, green							6.5±0.2	1.5	
	27	09470500027		0.5			0.5										
	26	09470500026		100			100										
	25	09470500025		90			90										
	24	09470500024		80			80										
	23	09470500023		70			70										
F	22	09470500022		60	RJ45 Ethernet standard cable, AWG22/1, 2x2x0.64, PVC, Cat. 5+, green	6.5±0.2	60	RJ45 Ethernet trailing cable, AWG22/7, 2x2x0.75, PUR, Cat. 5+, green							6.5±0.2	60	
	21	09470500021		50			50										
	20	09470500020		40			40										
	19	09470500019		30			30										
	18	09470500018		20			20										
	17	09470500017		15			15										
G	16	09470500016		10	RJ45 Ethernet standard cable, AWG22/1, 2x2x0.64, PVC, Cat. 5+, green	6.5±0.2	10	RJ45 Ethernet trailing cable, AWG22/7, 2x2x0.75, PUR, Cat. 5+, green							6.5±0.2	10	
	15	09470500015		9			9										
	14	09470500014		8			8										
	13	09470500013		7			7										
	12	09470500012		6			6										
	11	09470500011		5			5										
H	10	09470500010		4	RJ45 Ethernet standard cable, AWG22/1, 2x2x0.64, PVC, Cat. 5+, green	6.5±0.2	4	RJ45 Ethernet trailing cable, AWG22/7, 2x2x0.75, PUR, Cat. 5+, green							6.5±0.2	4	
	9	09470500009		3			3										
	8	09470500008		2			2										
	7	09470500007		1.5			1.5										
	6	09470500006		1			1										
	5	09470500005		0.5			0.5										
I	4	09470500004		0.5	RJ45 Ethernet standard cable, AWG22/1, 2x2x0.64, PVC, Cat. 5+, green	6.5±0.2	0.5	RJ45 Ethernet trailing cable, AWG22/7, 2x2x0.75, PUR, Cat. 5+, green							6.5±0.2	0.5	
	3	09470500003		0.5			0.5										
	2	09470500002		0.5			0.5										
	1	09470500001		0.5			0.5										
	Cont. no.	Part no.		Type of cable			Dim. d [mm]									Dim. a [m]	
	Cont. no.	Part no.		Type of cable			Dim. d [mm]									Dim. a [m]	

	All rights reserved		Created by	Inspected by	Standardisation	Date	State	
	Department EC PD - RO		MUNTEANV	AVRAM	HOFFMANN	2016-01-25	Final Release	
	Title						Doc-Key / ECM-Nr.	
HARTING Electronics GmbH			RJ Industrial Cable Assembly				100081066/UGD/014/D 500000099449	
D-32339 Espelkamp			Type	Number			Rev.	Page
			TB	094705000XX			D	2/2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HARTING:

09470500089