





Mating face according to : MIL-C-24308 / DIN 41652 / CECC 75301-802



Connector retention and insertion forces on the PCB = 25 / 80 newtons

							Dat.	Name		D-Sub, male, standard angle, 15 poles, with solder pin, screw lock and grounding board lock	Maßstab/ Scale 1.5:1	
						Detail.	15/dec/00	ALSPACE				
						Insp.						All Dim. in mm
						Stand.						Orig. Size DIN A 4
09 65 262 6813	4-40 UNC	2										
09 65 262 7813	4-40 UNC	3	29689	02/07/01	AA	HARTING EURL F-95972 Paris					TB 0965262x81x	Blatt/ Page 6 / 6
09 65 262 5813	4-40 UNC	0.76 µm Au	27960	15/dec/00	ALSPACE							
Part number	Screw lock thread	Performance level	Mod.	Dat.	Name					Sub.		

09 65 262 6813
D-Sub - S PCB connector

Other applications

gender	male connector, right angled
Termination	Stamped solder pins
shell	tinned metal shell with dimples
Number of contacts	15 way
Row pitch	Row separation 2.54 mm
Board fixing	with grounding board locks
flange	with screw lock UNC 4-40
Performance level	Performance level 2
Material	PBTP

Note: Obligatory information about HARTING products can be obtained exclusively from the data sheets.

Inquiry

The data sheet is up to date

2D files

PDF

DXF

09 65 262 5813
D-Sub - S PCB connector

Other applications

gender	male connector, right angled
Termination	Stamped solder pins
shell	tinned metal shell with dimples
Number of contacts	15 way
Row pitch	Row separation 2.54 mm
Board fixing	with grounding board locks
flange	with screw lock UNC 4-40
Performance level	Performance level S4
Material	PBTP

Note: Obligatory information about HARTING products can be obtained exclusively from the data sheets.



Data sheets are available in following formats
2D files

Typenblatt

Typenblatt

09 65 262 7813
D-Sub - S PCB connector

Other applications

gender	male connector, right angled
Termination	Stamped solder pins
shell	tinned metal shell with dimples
Number of contacts	15 way
Row pitch	Row separation 2.54 mm
Board fixing	with grounding board locks
flange	with screw lock UNC 4-40
Performance level	Performance level 3
Material	PBTP

Note: Obligatory information about HARTING products can be obtained exclusively from the data sheets.

Inquiry

The data sheet is up to date

2D files

PDF

DXF

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09652625813](#)