

NOTES:

1. MATERIALS AND FINISHES:

REVERSE POLARITY SMA BULKHEAD CRIMP JACK IP 67 - P/N: 132422RP-10
 MICRO COAX RIGHT ANGLE PLUG TERMINATED USING 1.13 MM CABLE - P/N: A-1PA-113-XXXB2



2. ELECTRICAL:

A. IMPEDANCE: 50 OHM, NOMINAL

3. PACKAGING:

A. QUANTITY: SINGLE PACK
 B. BAG TO BE MARKED: AMPHENOL RF, 336320-12-XXXX, AND DATE CODE

336320-12-XXXX		REVISIONS			
DRAWING NO.	REV	DESCRIPTION	DATE	ECO	APPR
THIRD ANGLE PROJ.	A	RELEASE TO MFG.	17-Dec-14	2838	CL/BCG



CONNEX NUMBER	CABLE LENGTH (IN)	CABLE LENGTH (MM)
336320-12-0050	1.968±0.150	50±3.81
336320-12-0100	3.936±0.150	100±3.81
336320-12-0150	5.905±0.150	150±3.81
336320-12-0200	7.873±0.200	200±5.08
336320-12-0250	9.842±0.200	250±5.08
336320-12-0300	11.810±0.200	300±5.08

* ADDITIONAL LENGTHS CAN BE PROVIDED.
 CONTACT AMPHENOL RF MARKETING FOR QUOTE

DESIGN REQUIREMENTS:

- | | |
|--|--|
| <input checked="" type="checkbox"/> FREQUENCY: DC TO 6 GHz | <input checked="" type="checkbox"/> CONTINUITY |
| <input type="checkbox"/> VSWR _____ : 1 MAX | <input checked="" type="checkbox"/> HI-POT :200 VRMS |
| <input type="checkbox"/> INS. LOSS _____ dB MAX | <input type="checkbox"/> OTHER |

CUSTOMER OUTLINE DRAWING

ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES AND TOLERANCES ARE:
 2 PLACE DECIMAL 3 PLACE DECIMAL ANGLES
 ±.015 (0,381 mm) ±.005 (0,127 mm) ± 1°

NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol Corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. The furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights or permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.

MATERIAL	DRAWN	DATE	TITLE	Amphenol Connex SCALE: 5.0:1 SHEET 2 OF 2	
SEE NOTES	CLEMENT	18-Nov-14	REVERSE POLARITY SMA BULKHEAD CRIMP JACK IP 67 TO AMC RIGHT ANGLE PLUG TERMINATED USING 1.13 MM CABLE, VARIOUS LENGTHS		
REFERENCE	ENGINEER	DATE			
EAR : 6511	CLEMENT	18-Nov-14			
	APPROVED	DATE	DWG SIZE	DRAWING NO.	REV
	B.C. GLEISSNER	17-Dec-14	B	336320-12-XXXX	A
	CAD FILE				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[336320-12-0050](#) [336320-12-0100](#) [336320-12-0150](#) [336320-12-0200](#) [336320-12-0250](#) [336320-12-0300](#)