

# N-Type Str Terminator Jk 50 Ohm Without Chain

o82-66g3

Find In Stock & Buy Now

N-Type Straight Terminator Jack 18 GHz 2 Watts Without Chain

+ Add To Parts List

⋮ Add To Compare


## Product Compliance

- RoHS (EU). Compliant with Exemption 6C - [View Certificate](#)
- California residents see [Prop 65 Warning](#)
- Additional compliance information is available in our [Compliance Center](#).

## Description

N-Type Straight Terminator Jack 18 GHz 2 Watts Without Chain

### Downloads

 o82-66g3 PDF Customer Drawing (Size: 261 kb)

## Product Life Cycle

Part Status	Active
-------------	--------

## Product Specifications

Body Finish	Nickel
Body Material	Brass
Chain Option	Without Chain
Contact Finish	Gold
Contact Material	Beryllium Copper
Export Control Classification Number	EAR99
Gender	Jack

IP Rating	Not Rated
Impedance (Ohms)	50
Insulator Material	PTFE
Isolated	No
Low PIM	No
Mil Qualified	No
Non Magnetic	No
Orientation	Straight
Panel Mounting Feature	Not Applicable
Power (Max Watts)	2
Temp (Max Degrees Celsius)	165
Temp (Min Degrees Celsius)	-65
Thread Direction	Standard

You May Also Be Interested In



N-Type Terminator PL  
50 Ohm Without Chain  
202109



N-Type Terminator PL  
18 GHz 50 Ohm 2 Watts  
Without Chain  
082-6694



N-Type Terminator PL  
50 Ohm Without Chain  
202109-10



Amphenol® RF



N-Type Terminator PL  
50 Ohm With Chain  
202109-11



N-Type Terminator Jk  
50 Ohm 5% 1 Watt  
082-5721-10RFX

Feedback

Need A Custom RF Cable Assembly?

Build Your Cable Now



## Subscribe And Stay Connected With Amphenol RF

[Submit](#)

By submitting your email, you are agreeing to receive occasional updates from Amphenol RF.  
This site is protected by reCAPTCHA and the Google. [Privacy Policy](#) and [Terms of Service](#) apply.

### Company

[About Us](#)  
[Locations](#)  
[Careers](#)  
[Newsroom](#)  
[Capabilities](#)  
[Quality](#)

### Quick Links

[Distributor Inventory](#)  
[Competitor Cross Reference](#)  
[Compliance Center](#)  
[Document Library](#)  
[Quickbuild RF](#)  
[Anti-Slavery/Human Trafficking](#)

### Support

[Contact Us](#)  
[Local Representative Locator](#)  
[Authorized Distributors](#)

### Account

[Login / Sign Up](#)  
[My Parts List](#)

[Extranet Login](#)

### Follow Us



Copyright © 2020 Amphenol RF. All Rights Reserved.

[Copyright](#) | [Terms & Conditions](#) | [Privacy Policy](#) | [User Agreement](#) | [Logos](#) | [Amphenol.com](#)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[082-6693](#)