






NOTES: UNLESS OTHERWISE SPECIFIED


1. MATERIAL: THERMOPLASTIC, HOUSING COLOR: GREY
INSERT COLOR: PER KEY CONFIGURATION
2. RoHS COMPLIANT
3. MOISTURE RESISTANCE: IP68 (1M OF WATER FOR
A PERIOD OF 24 HOURS , MATED CONDITION)
4. TEMPERATURE RANGE: -55C~125C
5. USE WITH CONNECTORS ATM06-08SX*
(* = A,B,C,D KEYS; * = MODIFICATIONS AND/OR COLORS)
6. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.



KEY-B CONFIGURATION
P/N ATM06-08SB-CAP
INSERT COLOR: BLACK



KEY-C CONFIGURATION
P/N ATM06-08SC-CAP
INSERT COLOR: GREEN



KEY-D CONFIGURATION
P/N ATM06-08SD-CAP
INSERT COLOR: BROWN

REVISIONS					
REV	ECO	DESCRIPTION	DATE	BY	APPR
A1	-	RELEASE	26JUN15	JAH	
A2	-	REVISED COLOR AND IP RATING	20NOV2020	JAH	DH

TITLE: PROTECTIVE CAP, 8 POSITION, ATM-SERIES
DWG NO.: ATM06-08SX-CAP
REV: A2
SH: 1
OF: 1

SEE KEY OPTIONS		DESCRIPTION		ITEM			
PART NUMBER							
QUANTITY	MATERIALS LIST						
UNLESS OTHERWISE SPECIFIED: 1) All dimensions are in metric (mm). 2) Tolerances are as follows: 1 PL DEC ±0.30 2 PL DEC ±0.15 3 PL DEC ±0.08 Fractions ±1/64 Angles ±1° 3) Note reference =							
SIGNATURES		DATE					
DRAWN: J. HEAD		23JUN2015					
CHECKED:							
ENGINEER:							
APPROVAL:							
MATERIAL SPECIFICATIONS:		CUSTOMER:					
PROCESS SPECIFICATIONS:		THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS.					
NEXT ASSY:							
 Sine Systems - www.amphenol-sine.com 44724 Morley Drive Clinton Township, MI 48036							
PROTECTIVE CAP, 8 POSITION, ATM-SERIES							
SIZE: B	TYPE: C-	DWG NO: ATM06-08SX-CAP	REVISION: A2				
SCALE: NONE		SHEET 1 OF 1					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[ATM06-08SB-CAP](#)