

NOTES:


1. MATERIALS AND FINISHES:  
 BNC R/A CRIMP PLUG - BRASS, NICKEL PLATED  
 CABLE - RG-59
2. ELECTRICAL:  
 A. IMPEDANCE: 75 OHM
3. PACKAGING:  
 A. QUANTITY: SINGLE PACK  
 B. MARKING: BAG TO BE MARKED  
 "AMPHENOL RF, 115104-15-XX.XX, AND DATE CODE"

THIRD ANGLE PROJ.

REVISIONS

REV	DESCRIPTION	DATE	ECN	APPR
A	RELEASE TO MFG.	11-Nov-10	--	KR
B	NO CHANGES TO THIS SHEET	03-Apr-13	2463	MB
C	NO CHANGES TO THIS SHEET	12-Feb-18	06882	BEW
D	ADD CUSTOMER DRAWING SHEET, 18 AND 48 IN LENGTHS	14-Mar-18	07301	BEW

LENGHT XX.XX (SEE TABLE)



LENGTH TABLE	
PART NUMBER	LENGTH INCHES (X)
115104-15-06.00	6.00
115104-15-12.00	12.00
115104-15-18.00	18.00
115104-15-24.00	24.00
115104-15-36.00	36.00
115104-15-48.00	48.00

\* ADDITIONAL LENGTH CAN BE PROVIDED BY CHANGING XX.XX TO DESIRED LEGNTH IN INCHES CONTACT CONNEX MARKETING FOR QUOTE

TOLERANCE TABLE	
LENGTH IN INCHES/FT [METERS]	TOLERANCE
0" - 23.90" [0 - 0.607]	±0.25" [0.006]
24.00" - 59.00" [0.610 - 1.499]	±0.50" [0.013]
5.0' - 24.9' [1.524 - 7.617]	±2.5%
25.0' & UP [7.620 & UP]	±5.0%

DESIGN REQUIREMENTS:

- |  |  |
|--|--|
| <input type="checkbox"/> FREQUENCY..... TO ..... GHz | <input checked="" type="checkbox"/> CONTINUITY         |
| <input type="checkbox"/> VSWR ..... : 1 MAX          | <input checked="" type="checkbox"/> HI-POT : 1000 VRMS |
| <input type="checkbox"/> INS. LOSS ..... dB MAX      | <input type="checkbox"/> OTHER                         |

**CUSTOMER OUTLINE DRAWING**  
 ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE: <0.5mm ±0.05mm    0.5 - 6mm ±0.1mm    6 - 30mm ±0.2mm    30 - 120mm ±0.3mm    ANGLES ±1°	MATERIAL	DRAWN	DATE	TITLE	Amphenol RF www.amphenolrf.com	
	REFERENCE	KARTHIK R	11-Nov-10	BNC R/A CRIMP PLUG TO BNC R/A CRIMP PLUG USING RG 59 CO-AXIAL CABLE, XX.XX LENGTH		
NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. the furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights to permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.	EAR# ---	KARTHIK R	11-Nov-10	SCALE: 1.8:1.0   SHEET 2 OF 2	DRAWING NO. 115104-15-XX.XX	
	REF:	K.CAPOZZI	15-Feb-18	DWG SIZE B	REV D	ITEM NO. 115104-15-XX.XX
	CONFIGURATION LEVEL: In Work	CAD FILE				PART NO. 115104-15-XX-XX
FINISH						

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[115104-15-48.00](#) [115104-15-18.00](#)