


NOTES:

- 1) LABELS ARE M23053/5 ,WHITE. ACCEPTABLE SUBSTITUTION IS DAT-38-292 OR TRANSVINYL (DAT-63-292-2.5).
- 2) DO NOT INSTALL CAPTIVATOR. PUT CAPTIVATOR IN SMALL ZIPLOCK BAG ATTACHED TO CABLE ASSEMBLY.
- 3) TERMINUS ENFACE REQUIREMENTS SHALL MEET GR-326 AND IEC 61300-3-35.
- 4) MAX IL @ 1310 nm SHALL BE 0.5 dB PER CONNECTION.

REVISION HISTORY - ALL SHEETS ARE AT THE SAME REVISION			
REV	DESCRIPTION	DATE	APPROVED
-	INITIAL RELEASE	2017/11/13	



AFSI PROPRIETARY

4	AFSI-PRE T BOX	BOX, SMALL FIBER CABLE 10X10X2 W/AFSI GRAPHICS	1
3	M85045/16-02	CABLE, MIL-SPEC SHIPBRD, 1-FBR, SM 8.3/125um	8.6 FEET
2	MSTC2000	ST CONNECTOR, SM, 126um (M83522/16-DNY)	1
1	M29504/15-4181C	QPL SOCKET TERM. 126UM, SM WITH CRIMP, SYMB 4181	1
ITEM NO.	PART NO.	DESCRIPTION	QTY/ LENGTH

MATERIAL:		DFTR/Designer: C. Hoang	2017/10/20	<b>Amphenol FSI</b>
		Check By: B. Waite	2017/10/24	
		Manufacturing: B. Waite	2017/10/24	
		Market Manager/PLM: Q. Abraham	2017/10/25	
		Configuration Management: L. Brown	2017/11/13	TITLE: SIMPLEX /15 TERMINI TO MIL ST ASSEMBLY, SM
DRILLED HOLE DIAMETER TOLERANCE				
<small>           0.000 TO 0.125 <sup>+0.001</sup>/<sub>-0.001</sub>    0.251 TO 0.500 <sup>+0.002</sup>/<sub>-0.002</sub>            0.126 TO 0.250 <sup>+0.001</sup>/<sub>-0.001</sub>    0.501 TO 0.750 <sup>+0.002</sup>/<sub>-0.002</sub> </small>				
DO NOT SCALE DRAWING				
<small>           UNLESS OTHERWISE SPECIFIED            DIMENSIONS ARE IN INCHES            TOL ON ANGLES ±3°            1 PL ±.1    2 PL ±.02    3 PL ±.010            INTERPRET DIM AND TOL PER            ASME 14.2M-1994         </small>		<small>           This Document contains proprietary information and such information is prohibited from disclosure to others, publication or duplication in whole or in part without written permission from Amphenol Fiber Systems International.            Copyright © 2017 Amphenol Fiber Systems International.            Non published work. All rights reserved.         </small>		
NEXT ASSY	USED ON	SIZE <b>A</b>	CAGE CODE <b>OYPM2</b>	DWG NO <b>13100403MD-D6</b>
APPLICATION		SCALE: NONE	SHEET 1 OF 1	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[13100403MD-D6](#)